

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264425

Luminaire Tested: P3AS05R559730DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264425
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559730DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 380.0 lumens
Efficiency: N/A
Efficacy: 52.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264425

CATALOG NUMBER: P3AS05R559730DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1264425

CATALOG NUMBER: P3AS05R559730DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	96		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71442
5°	70548
10°	67756
15°	63383
20°	57802
25°	51584
30°	45121
35°	37477
40°	29541
45°	20033
50°	12247
55°	6346
60°	5921
65°	5604
70°	5193
75°	4575
80°	4546
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20033 cd/sqm

TEST NUMBER: P1264425

CATALOG NUMBER: P3AS05R559730DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.1	7.9
10°-20°	78.0	20.5
20°-30°	97.7	25.7
30°-40°	87.2	23.0
40°-50°	51.1	13.4
50°-60°	17.6	4.6
60°-70°	10.7	2.8
70°-80°	5.9	1.6
80°-90°	1.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	205.8	54.2
0°-40°	293.0	77.1
0°-60°	361.7	95.2
0°-90°	380.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	380.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	326	
5°	320	30
15°	279	78
25°	213	98
35°	140	87
45°	65	51
55°	17	18
65°	11	11
75°	5	6
85°	1	2
90°	0	

TEST NUMBER: P1264425

CATALOG NUMBER: P3AS05R559730DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	325.8
2.5°	324.0
5°	320.5
7.5°	313.3
10°	304.3
12.5°	293.1
15°	279.2
17.5°	264.3
20°	247.7
22.5°	230.7
25°	213.2
27.5°	195.7
30°	178.2
32.5°	159.3
35°	140.0
37.5°	121.2
40°	103.2
42.5°	83.9
45°	64.6
47.5°	49.4
50°	35.9
52.5°	23.3
55°	16.6
57.5°	14.8
60°	13.5
62.5°	12.1
65°	10.8
67.5°	9.4
70°	8.1
72.5°	6.7
75°	5.4
77.5°	4.5
80°	3.6
82.5°	2.2
85°	1.3
87.5°	0.9
90°	0.0

(END OF REPORT)