

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265126

Luminaire Tested: P3AS13R409730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 382.1 lumens
Efficiency: N/A
Efficacy: 26.2 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265126

CATALOG NUMBER: P3AS13R409730DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265126

CATALOG NUMBER: P3AS13R409730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85761
5°	84195
10°	79357
15°	72078
20°	63332
25°	54076
30°	44792
35°	34559
40°	24589
45°	16560
50°	9040
55°	6384
60°	6008
65°	5552
70°	4937
75°	4745
80°	3788
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16560 cd/sqm

TEST NUMBER: P1265126

CATALOG NUMBER: P3AS13R409730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.7	9.3
10°-20°	88.4	23.2
20°-30°	102.2	26.8
30°-40°	80.6	21.1
40°-50°	41.4	10.8
50°-60°	15.8	4.1
60°-70°	10.5	2.7
70°-80°	5.7	1.5
80°-90°	1.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	226.4	59.3
0°-40°	307.0	80.3
0°-60°	364.2	95.3
0°-90°	382.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	382.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	391	
5°	382	36
15°	318	88
25°	224	102
35°	129	81
45°	53	41
55°	17	16
65°	11	10
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P1265126

CATALOG NUMBER: P3AS13R409730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	391.1
2.5°	388.9
5°	382.5
7.5°	371.4
10°	356.4
12.5°	338.9
15°	317.5
17.5°	295.3
20°	271.4
22.5°	247.0
25°	223.5
27.5°	200.0
30°	176.9
32.5°	153.4
35°	129.1
37.5°	106.4
40°	85.9
42.5°	68.4
45°	53.4
47.5°	38.9
50°	26.5
52.5°	19.2
55°	16.7
57.5°	15.0
60°	13.7
62.5°	12.0
65°	10.7
67.5°	9.0
70°	7.7
72.5°	6.4
75°	5.6
77.5°	4.3
80°	3.0
82.5°	2.6
85°	1.3
87.5°	0.9
90°	0.0

(END OF REPORT)