

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264431

Luminaire Tested: P3AS05R559730DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264431
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559730DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 326.9 lumens
Efficiency: N/A
Efficacy: 45.4 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264431

CATALOG NUMBER: P3AS05R559730DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1264431

CATALOG NUMBER: P3AS05R559730DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		86
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88962
5°	86727
10°	80626
15°	71805
20°	61022
25°	49237
30°	37525
35°	26689
40°	17604
45°	10451
50°	6141
55°	3785
60°	3333
65°	3009
70°	2565
75°	2288
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10451 cd/sqm

TEST NUMBER: P1264431

CATALOG NUMBER: P3AS05R559730DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.6	11.2
10°-20°	87.7	26.8
20°-30°	92.9	28.4
30°-40°	62.7	19.2
40°-50°	27.5	8.4
50°-60°	9.9	3.0
60°-70°	5.7	1.8
70°-80°	3.0	0.9
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	217.1	66.4
0°-40°	279.9	85.6
0°-60°	317.2	97.0
0°-90°	326.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	326.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	406	
5°	394	37
15°	316	88
25°	204	93
35°	100	63
45°	34	28
55°	10	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1264431

CATALOG NUMBER: P3AS05R559730DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	405.7
2.5°	402.5
5°	394.0
7.5°	380.1
10°	362.1
12.5°	340.5
15°	316.3
17.5°	289.3
20°	261.5
22.5°	232.3
25°	203.5
27.5°	175.2
30°	148.2
32.5°	122.6
35°	99.7
37.5°	79.1
40°	61.5
42.5°	46.3
45°	33.7
47.5°	24.7
50°	18.0
52.5°	12.6
55°	9.9
57.5°	9.0
60°	7.6
62.5°	6.7
65°	5.8
67.5°	4.9
70°	4.0
72.5°	3.6
75°	2.7
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)