

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265132

Luminaire Tested: P3AS13R409730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265132
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 314.0 lumens
Efficiency: N/A
Efficacy: 21.5 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265132

CATALOG NUMBER: P3AS13R409730DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265132

CATALOG NUMBER: P3AS13R409730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97777
5°	95795
10°	89199
15°	77730
20°	62655
25°	46962
30°	33018
35°	21630
40°	13082
45°	7815
50°	4674
55°	3747
60°	3377
65°	2906
70°	2757
75°	2203
80°	2147
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7815 cd/sqm

TEST NUMBER: P1265132

CATALOG NUMBER: P3AS13R409730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.4	12.9
10°-20°	94.3	30.0
20°-30°	88.9	28.3
30°-40°	51.4	16.4
40°-50°	20.5	6.5
50°-60°	9.1	2.9
60°-70°	5.6	1.8
70°-80°	2.9	0.9
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	223.6	71.2
0°-40°	275.0	87.6
0°-60°	304.5	97.0
0°-90°	314.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	314.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	446	
5°	435	40
15°	342	94
25°	194	89
35°	81	51
45°	25	20
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1265132

CATALOG NUMBER: P3AS13R409730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	445.9
2.5°	443.3
5°	435.2
7.5°	420.2
10°	400.6
12.5°	374.1
15°	342.4
17.5°	306.9
20°	268.5
22.5°	230.0
25°	194.1
27.5°	160.7
30°	130.4
32.5°	103.9
35°	80.8
37.5°	61.1
40°	45.7
42.5°	34.2
45°	25.2
47.5°	18.4
50°	13.7
52.5°	11.1
55°	9.8
57.5°	9.0
60°	7.7
62.5°	6.4
65°	5.6
67.5°	4.7
70°	4.3
72.5°	3.4
75°	2.6
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)