

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264433

Luminaire Tested: P3AS05R609730DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609730DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 579.9 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264433

CATALOG NUMBER: P3AS05R609730DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1264433

CATALOG NUMBER: P3AS05R609730DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138498
5°	132995
10°	136938
15°	138707
20°	122464
25°	103216
30°	83709
35°	54529
40°	25047
45°	9613
50°	3207
55°	841
60°	789
65°	675
70°	577
75°	763
80°	505
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9613 cd/sqm

TEST NUMBER: P1264433

CATALOG NUMBER: P3AS05R609730DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.2	10.0
10°-20°	167.3	28.9
20°-30°	195.1	33.7
30°-40°	125.9	21.7
40°-50°	28.2	4.9
50°-60°	2.8	0.5
60°-70°	1.3	0.2
70°-80°	0.8	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	420.6	72.5
0°-40°	546.6	94.3
0°-60°	577.6	99.6
0°-90°	579.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	579.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	632	
5°	604	58
15°	611	167
25°	427	195
35°	204	126
45°	31	28
55°	2	3
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264433

CATALOG NUMBER: P3AS05R609730DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	631.6
2.5°	621.3
5°	604.2
7.5°	603.4
10°	615.0
12.5°	622.6
15°	611.0
17.5°	576.0
20°	524.8
22.5°	471.5
25°	426.6
27.5°	382.6
30°	330.6
32.5°	269.6
35°	203.7
37.5°	139.1
40°	87.5
42.5°	52.5
45°	31.0
47.5°	17.9
50°	9.4
52.5°	3.1
55°	2.2
57.5°	1.8
60°	1.8
62.5°	1.3
65°	1.3
67.5°	1.3
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)