

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265140

Luminaire Tested: P3AS13R459730DE010 E3CB1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1265140  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R459730DE010 E3CB1MW  
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3CB1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1168.0 lumens  
Efficiency: N/A  
Efficacy: 80.0 lumens/watt  
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265140  
CATALOG NUMBER: P3AS13R459730DE010 E3CB1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1265140  
 CATALOG NUMBER: P3AS13R459730DE010 E3CB1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87	87	87	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	79	79	79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75	75	75	75
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	64	64	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	506385
5°	509090
10°	493444
15°	413510
20°	316101
25°	192422
30°	80063
35°	25645
40°	7986
45°	1613
50°	1194
55°	1338
60°	1140
65°	1349
70°	1090
75°	1440
80°	1137
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1613 cd/sqm



TEST NUMBER: P1265140  
 CATALOG NUMBER: P3AS13R459730DE010 E3CB1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	218.1	18.7
10°-20°	500.6	42.9
20°-30°	360.5	30.9
30°-40°	75.0	6.4
40°-50°	6.9	0.6
50°-60°	2.8	0.2
60°-70°	2.2	0.2
70°-80°	1.5	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1079.2	92.4
0°-40°	1154.2	98.8
0°-60°	1163.9	99.7
0°-90°	1168.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1168.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2309	
5°	2313	218
15°	1822	501
25°	795	360
35°	96	75
45°	5	7
55°	4	3
65°	3	2
75°	2	1
85°	0	0
90°	0	

TEST NUMBER: P1265140  
CATALOG NUMBER: P3AS13R459730DE010 E3CB1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2309.3
2.5°	2310.2
5°	2312.8
7.5°	2296.3
10°	2216.1
12.5°	2048.9
15°	1821.5
17.5°	1588.9
20°	1354.6
22.5°	1085.4
25°	795.3
27.5°	524.4
30°	316.2
32.5°	176.8
35°	95.8
37.5°	54.0
40°	27.9
42.5°	12.2
45°	5.2
47.5°	3.5
50°	3.5
52.5°	3.5
55°	3.5
57.5°	2.6
60°	2.6
62.5°	2.6
65°	2.6
67.5°	1.7
70°	1.7
72.5°	1.7
75°	1.7
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)