

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264498

Luminaire Tested: P3AS05R709730DE010 E3D1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1264498  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R709730DE010 E3D1MW  
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3D1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 561.9 lumens  
Efficiency: N/A  
Efficacy: 78.0 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1264498  
CATALOG NUMBER: P3AS05R709730DE010 E3D1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1264498  
 CATALOG NUMBER: P3AS05R709730DE010 E3D1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78			
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53			
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	111592
5°	106493
10°	101312
15°	98616
20°	94975
25°	89884
30°	83608
35°	70216
40°	45256
45°	21025
50°	5526
55°	1376
60°	1360
65°	1141
70°	1154
75°	1101
80°	1137
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 21025 cd/sqm



TEST NUMBER: P1264498  
 CATALOG NUMBER: P3AS05R709730DE010 E3D1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.3	8.1
10°-20°	122.1	21.7
20°-30°	170.5	30.3
30°-40°	158.1	28.1
40°-50°	56.7	10.1
50°-60°	4.8	0.9
60°-70°	2.4	0.4
70°-80°	1.5	0.3
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	337.9	60.1
0°-40°	496.0	88.3
0°-60°	557.5	99.2
0°-90°	561.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	561.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	509	
5°	484	45
15°	434	122
25°	372	171
35°	262	158
45°	68	57
55°	4	5
65°	2	2
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P1264498  
CATALOG NUMBER: P3AS05R709730DE010 E3D1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	508.9
2.5°	501.3
5°	483.8
7.5°	467.6
10°	455.0
12.5°	444.7
15°	434.4
17.5°	421.8
20°	407.0
22.5°	389.9
25°	371.5
27.5°	352.6
30°	330.2
32.5°	301.4
35°	262.3
37.5°	212.5
40°	158.1
42.5°	107.8
45°	67.8
47.5°	37.7
50°	16.2
52.5°	5.4
55°	3.6
57.5°	3.1
60°	3.1
62.5°	2.7
65°	2.2
67.5°	2.2
70°	1.8
72.5°	1.8
75°	1.3
77.5°	1.3
80°	0.9
82.5°	0.9
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)