

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264500

Luminaire Tested: P3AS05R709730DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264500
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709730DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 536.0 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264500

CATALOG NUMBER: P3AS05R709730DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1264500

CATALOG NUMBER: P3AS05R709730DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		86
4	95	87	81	77	94	86	81	77	84	79	76		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104224
5°	98261
10°	93185
15°	91510
20°	88208
25°	83134
30°	82544
35°	71902
40°	46516
45°	21987
50°	3070
55°	268
60°	175
65°	208
70°	128
75°	169
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21987 cd/sqm

TEST NUMBER: P1264500

CATALOG NUMBER: P3AS05R709730DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.7	7.8
10°-20°	113.2	21.1
20°-30°	160.1	29.9
30°-40°	160.9	30.0
40°-50°	57.9	10.8
50°-60°	1.6	0.3
60°-70°	0.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	315.0	58.8
0°-40°	476.0	88.8
0°-60°	535.4	99.9
0°-90°	536.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	536.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	475	
5°	446	42
15°	403	113
25°	344	160
35°	269	161
45°	71	58
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1264500

CATALOG NUMBER: P3AS05R709730DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	475.3
1°	474.0
2°	469.8
3°	463.2
4°	454.8
5°	446.4
6°	438.5
7°	432.4
8°	426.9
9°	422.5
10°	418.5
11°	415.2
12°	412.1
13°	409.0
14°	406.2
15°	403.1
16°	399.3
17°	395.4
18°	390.5
19°	384.6
20°	378.0
21°	370.7
22°	363.5
23°	356.4
24°	349.6
25°	343.6
26°	339.5
27°	336.2
28°	333.5
29°	330.4
30°	326.0
31°	319.6
32°	310.6
32.5°	305.6
33°	298.7
34°	285.3
35°	268.6
36°	250.1
37°	229.2
37.5°	219.5
38°	206.3
39°	182.7
40°	162.5
42.5°	112.5
45°	70.9



TEST NUMBER: P1264500

CATALOG NUMBER: P3AS05R709730DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	38.1
50°	9.0
52.5°	1.1
55°	0.7
57.5°	0.7
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)