

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265162

Luminaire Tested: P3AS13R459730DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265162
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459730DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 628.0 lumens
Efficiency: N/A
Efficacy: 43.0 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265162

CATALOG NUMBER: P3AS13R459730DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1265162

CATALOG NUMBER: P3AS13R459730DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	62	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	187046
5°	182786
10°	168623
15°	146630
20°	120457
25°	93731
30°	69201
35°	48693
40°	30400
45°	16467
50°	8904
55°	7646
60°	6885
65°	5863
70°	5001
75°	5168
80°	4420
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16467 cd/sqm

TEST NUMBER: P1265162

CATALOG NUMBER: P3AS13R459730DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.9	12.2
10°-20°	178.6	28.4
20°-30°	177.3	28.2
30°-40°	114.2	18.2
40°-50°	44.0	7.0
50°-60°	17.9	2.8
60°-70°	11.3	1.8
70°-80°	6.1	1.0
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	432.7	68.9
0°-40°	546.9	87.1
0°-60°	608.7	96.9
0°-90°	628.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	628.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	853	
5°	830	77
15°	646	179
25°	387	177
35°	182	114
45°	53	44
55°	20	18
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1265162

CATALOG NUMBER: P3AS13R459730DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	853.0
2.5°	848.7
5°	830.4
7.5°	799.1
10°	757.3
12.5°	705.1
15°	645.9
17.5°	581.5
20°	516.2
22.5°	450.0
25°	387.4
27.5°	328.2
30°	273.3
32.5°	225.4
35°	181.9
37.5°	142.8
40°	106.2
42.5°	76.6
45°	53.1
47.5°	35.7
50°	26.1
52.5°	21.8
55°	20.0
57.5°	17.4
60°	15.7
62.5°	13.1
65°	11.3
67.5°	9.6
70°	7.8
72.5°	7.0
75°	6.1
77.5°	4.4
80°	3.5
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)