

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265174

Luminaire Tested: P3AS13R509730DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1265174  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R509730DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 480.0 lumens  
Efficiency: N/A  
Efficacy: 32.9 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265174  
CATALOG NUMBER: P3AS13R509730DE010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1265174  
 CATALOG NUMBER: P3AS13R509730DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87				87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82				82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76				76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67				67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64				64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60				60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57				57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54				54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	152817
5°	149746
10°	140256
15°	125563
20°	105663
25°	80642
30°	52413
35°	31079
40°	17948
45°	8993
50°	3343
55°	2600
60°	2412
65°	2231
70°	2180
75°	2203
80°	2147
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8993 cd/sqm



TEST NUMBER: P1265174

CATALOG NUMBER: P3AS13R509730DE010 E3DL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.3	13.2
10°-20°	153.0	31.9
20°-30°	150.1	31.3
30°-40°	75.6	15.8
40°-50°	23.9	5.0
50°-60°	6.2	1.3
60°-70°	4.4	0.9
70°-80°	2.7	0.6
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	366.3	76.3
0°-40°	441.9	92.1
0°-60°	472.0	98.3
0°-90°	480.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	480.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	697	
5°	680	63
15°	553	153
25°	333	150
35°	116	76
45°	29	24
55°	7	6
65°	4	4
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1265174  
CATALOG NUMBER: P3AS13R509730DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	696.9
2.5°	692.7
5°	680.3
7.5°	658.1
10°	629.9
12.5°	593.6
15°	553.1
17.5°	506.2
20°	452.8
22.5°	395.2
25°	333.3
27.5°	267.6
30°	207.0
32.5°	155.8
35°	116.1
37.5°	85.8
40°	62.7
42.5°	44.4
45°	29.0
47.5°	16.6
50°	9.8
52.5°	7.3
55°	6.8
57.5°	6.0
60°	5.5
62.5°	5.1
65°	4.3
67.5°	3.8
70°	3.4
72.5°	3.0
75°	2.6
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)