

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265180

Luminaire Tested: P3AS13R509730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265180
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 374.1 lumens
Efficiency: N/A
Efficacy: 25.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265180
CATALOG NUMBER: P3AS13R509730DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1265180
 CATALOG NUMBER: P3AS13R509730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76003
5°	74884
10°	71564
15°	66289
20°	59575
25°	52358
30°	44538
35°	36112
40°	27137
45°	17459
50°	8290
55°	6537
60°	6184
65°	5759
70°	5193
75°	4660
80°	4293
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17459 cd/sqm



TEST NUMBER: P1265180
 CATALOG NUMBER: P3AS13R509730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.9	8.5
10°-20°	81.4	21.8
20°-30°	98.9	26.4
30°-40°	83.9	22.4
40°-50°	43.6	11.7
50°-60°	15.7	4.2
60°-70°	10.9	2.9
70°-80°	5.9	1.6
80°-90°	1.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	212.2	56.7
0°-40°	296.1	79.2
0°-60°	355.4	95.0
0°-90°	374.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	374.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	347	
5°	340	32
15°	292	81
25°	216	99
35°	135	84
45°	56	44
55°	17	16
65°	11	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1265180
CATALOG NUMBER: P3AS13R509730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	346.6
2.5°	345.3
5°	340.2
7.5°	332.5
10°	321.4
12.5°	307.3
15°	292.0
17.5°	274.5
20°	255.3
22.5°	235.6
25°	216.4
27.5°	196.4
30°	175.9
32.5°	155.4
35°	134.9
37.5°	114.8
40°	94.8
42.5°	75.6
45°	56.3
47.5°	37.6
50°	24.3
52.5°	18.8
55°	17.1
57.5°	15.4
60°	14.1
62.5°	12.4
65°	11.1
67.5°	9.4
70°	8.1
72.5°	6.8
75°	5.5
77.5°	4.3
80°	3.4
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)