

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264561

Luminaire Tested: P3AS09R159730DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264561
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159730DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 681.0 lumens
Efficiency: N/A
Efficacy: 61.4 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264561
CATALOG NUMBER: P3AS09R159730DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1264561
 CATALOG NUMBER: P3AS09R159730DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	94	93	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	90	88	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	87	86	85	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	82	81	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80	80	79	78	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	77	76	75	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	74	73	72	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	72	71	70	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	69	68	67	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	67	66	65	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	581752
5°	516398
10°	358622
15°	212078
20°	120784
25°	69052
30°	38208
35°	20371
40°	11278
45°	6109
50°	3821
55°	3020
60°	2588
65°	2387
70°	2116
75°	2203
80°	1642
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6109 cd/sqm



TEST NUMBER: P1264561
 CATALOG NUMBER: P3AS09R159730DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.5	29.3
10°-20°	263.3	38.7
20°-30°	135.6	19.9
30°-40°	50.9	7.5
40°-50°	16.7	2.4
50°-60°	7.2	1.1
60°-70°	4.5	0.7
70°-80°	2.7	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	598.3	87.9
0°-40°	649.3	95.3
0°-60°	673.1	98.8
0°-90°	681.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	681.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2653	
5°	2346	199
15°	934	263
25°	285	136
35°	76	51
45°	20	17
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1264561
CATALOG NUMBER: P3AS09R159730DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2653.0
1°	2647.8
2°	2613.0
3°	2546.7
4°	2459.5
5°	2346.0
6°	2217.4
7°	2076.4
8°	1919.6
9°	1764.7
10°	1610.6
12.5°	1239.2
15°	934.2
17.5°	699.3
20°	517.6
22.5°	386.4
25°	285.4
27.5°	208.0
30°	150.9
32.5°	106.9
35°	76.1
37.5°	54.5
40°	39.4
42.5°	28.2
45°	19.7
47.5°	14.4
50°	11.2
52.5°	9.2
55°	7.9
57.5°	6.6
60°	5.9
62.5°	5.2
65°	4.6
67.5°	3.9
70°	3.3
72.5°	3.3
75°	2.6
77.5°	2.0
80°	1.3
82.5°	1.3
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)