

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265184

Luminaire Tested: P3AS13R509730DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265184
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509730DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 762.9 lumens
Efficiency: N/A
Efficacy: 52.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265184

CATALOG NUMBER: P3AS13R509730DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1265184

CATALOG NUMBER: P3AS13R509730DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103		110	107	104	102		103	101	99		99	97	96		95	94	93
2	106	100	95	91		103	98	94	90		95	91	88		92	89	86		89	86	84
3	99	92	86	81		97	90	85	81		88	83	79		85	81	78		83	80	77
4	93	85	78	73		91	83	77	73		81	76	72		79	75	71		77	73	70
5	88	78	72	67		86	77	71	66		75	70	66		74	69	65		72	68	64
6	83	73	66	61		81	72	65	61		70	65	60		69	64	60		67	63	59
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	57	52		73	63	56	52		61	56	52		60	55	51		59	55	51
9	70	59	53	48		69	59	52	48		58	52	48		57	52	48		56	51	48
10	66	56	49	45		65	55	49	45		54	49	45		54	48	45		53	48	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	155053
5°	152762
10°	146000
15°	135211
20°	121531
25°	106821
30°	90849
35°	73669
40°	55332
45°	35632
50°	16921
55°	13304
60°	12587
65°	11726
70°	10579
75°	9574
80°	8840
85°	8806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35632 cd/sqm

TEST NUMBER: P1265184

CATALOG NUMBER: P3AS13R509730DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.1	8.5
10°-20°	166.1	21.8
20°-30°	201.8	26.4
30°-40°	171.1	22.4
40°-50°	88.9	11.6
50°-60°	32.0	4.2
60°-70°	22.2	2.9
70°-80°	12.0	1.6
80°-90°	3.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	432.9	56.7
0°-40°	604.0	79.2
0°-60°	724.9	95.0
0°-90°	762.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	762.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	707	
5°	694	65
15°	596	166
25°	442	202
35°	275	171
45°	115	89
55°	35	32
65°	23	22
75°	11	12
85°	4	4
90°	0	

TEST NUMBER: P1265184

CATALOG NUMBER: P3AS13R509730DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	707.1
2.5°	704.5
5°	694.0
7.5°	678.4
10°	655.7
12.5°	627.0
15°	595.6
17.5°	559.9
20°	520.8
22.5°	480.7
25°	441.5
27.5°	400.6
30°	358.8
32.5°	317.0
35°	275.2
37.5°	234.3
40°	193.3
42.5°	154.1
45°	114.9
47.5°	76.6
50°	49.6
52.5°	38.3
55°	34.8
57.5°	31.3
60°	28.7
62.5°	25.3
65°	22.6
67.5°	19.2
70°	16.5
72.5°	13.9
75°	11.3
77.5°	8.7
80°	7.0
82.5°	5.2
85°	3.5
87.5°	1.7
90°	0.0

(END OF REPORT)