

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265206

Luminaire Tested: P3AS13R559730DE010 E3DL1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1265206  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R559730DE010 E3DL1MW  
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3DL1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 950.0 lumens  
Efficiency: N/A  
Efficacy: 65.1 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265206  
CATALOG NUMBER: P3AS13R559730DE010 E3DL1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1265206  
 CATALOG NUMBER: P3AS13R559730DE010 E3DL1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	260856
5°	258221
10°	249361
15°	230489
20°	198911
25°	157098
30°	111435
35°	71849
40°	43167
45°	24313
50°	13066
55°	4664
60°	4210
65°	4047
70°	3911
75°	3728
80°	3283
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 24313 cd/sqm



TEST NUMBER: P1265206  
 CATALOG NUMBER: P3AS13R559730DE010 E3DL1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.3	11.6
10°-20°	280.8	29.6
20°-30°	294.2	31.0
30°-40°	171.6	18.1
40°-50°	64.2	6.8
50°-60°	15.1	1.6
60°-70°	7.8	0.8
70°-80°	4.6	0.5
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	685.3	72.1
0°-40°	857.0	90.2
0°-60°	936.3	98.6
0°-90°	950.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	950.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1190	
5°	1173	110
15°	1015	281
25°	649	294
35°	268	172
45°	78	64
55°	12	15
65°	8	8
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1265206  
CATALOG NUMBER: P3AS13R559730DE010 E3DL1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1189.6
2.5°	1186.1
5°	1173.1
7.5°	1152.2
10°	1119.9
12.5°	1074.6
15°	1015.3
17.5°	940.4
20°	852.4
22.5°	753.9
25°	649.3
27.5°	542.1
30°	440.1
32.5°	347.7
35°	268.4
37.5°	203.9
40°	150.8
42.5°	108.1
45°	78.4
47.5°	56.6
50°	38.3
52.5°	21.8
55°	12.2
57.5°	10.5
60°	9.6
62.5°	8.7
65°	7.8
67.5°	7.0
70°	6.1
72.5°	5.2
75°	4.4
77.5°	3.5
80°	2.6
82.5°	1.7
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)