

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264604

Luminaire Tested: P3AS09R209730DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264604
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209730DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 452.0 lumens
Efficiency: N/A
Efficacy: 40.7 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264604

CATALOG NUMBER: P3AS09R209730DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1264604

CATALOG NUMBER: P3AS09R209730DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87
3	98	90	83	78	95	88	82	78	85	81	77		83	79	75		80
4	92	82	75	70	90	81	75	70	79	73	69		77	72	68		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70
6	81	70	63	58	79	70	63	58	68	62	58		66	61	57		65
7	76	66	59	54	75	65	58	53	64	58	53		62	57	53		61
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57
9	69	58	51	46	67	57	51	46	56	50	46		55	50	46		54
10	65	54	48	43	64	54	48	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128191
5°	119084
10°	100844
15°	78933
20°	62119
25°	49503
30°	39829
35°	32471
40°	26850
45°	22638
50°	19377
55°	16668
60°	14560
65°	12764
70°	10963
75°	9658
80°	7198
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22638 cd/sqm

TEST NUMBER: P1264604

CATALOG NUMBER: P3AS09R209730DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.8	10.8
10°-20°	97.3	21.5
20°-30°	94.5	20.9
30°-40°	76.4	16.9
40°-50°	56.7	12.6
50°-60°	39.4	8.7
60°-70°	24.7	5.5
70°-80°	12.0	2.7
80°-90°	2.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	240.7	53.3
0°-40°	317.1	70.2
0°-60°	413.2	91.4
0°-90°	452.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	452.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	585	
5°	541	49
15°	348	97
25°	205	95
35°	121	76
45°	73	57
55°	44	39
65°	25	25
75°	11	12
85°	2	2
90°	0	

TEST NUMBER: P1264604

CATALOG NUMBER: P3AS09R209730DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	584.6
2.5°	571.3
5°	541.0
7.5°	500.3
10°	452.9
12.5°	400.8
15°	347.7
17.5°	304.1
20°	266.2
22.5°	233.1
25°	204.6
27.5°	180.0
30°	157.3
32.5°	138.3
35°	121.3
37.5°	106.1
40°	93.8
42.5°	82.4
45°	73.0
47.5°	64.4
50°	56.8
52.5°	50.2
55°	43.6
57.5°	37.9
60°	33.2
62.5°	29.4
65°	24.6
67.5°	20.8
70°	17.1
72.5°	14.2
75°	11.4
77.5°	8.5
80°	5.7
82.5°	2.8
85°	1.9
87.5°	0.0
90°	0.0

(END OF REPORT)