

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264616

Luminaire Tested: P3AS09R259730DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264616
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259730DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 887.0 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264616

CATALOG NUMBER: P3AS09R259730DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1264616

CATALOG NUMBER: P3AS09R259730DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		100
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		98
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	106	101	97	94	104	100	96	94	98	95	92		96	93	91		94
5	103	97	93	91	101	96	93	90	95	92	90		93	91	89		92
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		90
7	98	92	88	85	97	91	87	85	90	87	84		89	86	84		88
8	95	89	85	83	94	89	85	83	88	85	82		87	84	82		86
9	93	87	83	81	92	86	83	80	86	83	80		85	82	80		84
10	91	85	81	79	90	84	81	79	84	81	78		83	80	78		83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	971435
5°	899888
10°	696246
15°	332556
20°	109653
25°	46212
30°	17927
35°	7736
40°	2576
45°	1209
50°	443
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1209 cd/sqm

TEST NUMBER: P1264616

CATALOG NUMBER: P3AS09R259730DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	359.4	40.5
10°-20°	408.7	46.1
20°-30°	95.0	10.7
30°-40°	19.9	2.2
40°-50°	3.2	0.4
50°-60°	0.5	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	863.0	97.3
0°-40°	883.0	99.5
0°-60°	886.7	100.0
0°-90°	887.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	887.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4430	
5°	4088	359
15°	1465	409
25°	191	95
35°	29	20
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1264616

CATALOG NUMBER: P3AS09R259730DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4430.1
1°	4421.1
2°	4375.1
3°	4310.4
4°	4211.7
5°	4088.2
6°	3929.7
7°	3763.7
8°	3577.5
9°	3367.5
10°	3126.9
11°	2848.1
12°	2528.1
13°	2177.6
14°	1810.9
15°	1464.9
16°	1158.7
17°	902.7
18°	710.1
19°	568.0
20°	469.9
21°	392.7
22°	329.6
23°	275.3
24°	230.3
25°	191.0
27.5°	113.2
30°	70.8
32.5°	45.3
35°	28.9
37.5°	17.4
40°	9.0
42.5°	5.8
45°	3.9
47.5°	2.3
50°	1.3
52.5°	0.6
55°	0.6
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0



TEST NUMBER: P1264616

CATALOG NUMBER: P3AS09R259730DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)