

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265232

Luminaire Tested: P3AS13R609730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265232
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 449.0 lumens
Efficiency: N/A
Efficacy: 30.8 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265232

CATALOG NUMBER: P3AS13R609730DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265232

CATALOG NUMBER: P3AS13R609730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79		
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73		
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106022
5°	105018
10°	101958
15°	95528
20°	84544
25°	70722
30°	55426
35°	40207
40°	26764
45°	16684
50°	9040
55°	2600
60°	2412
65°	2231
70°	2180
75°	2203
80°	2147
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16684 cd/sqm

TEST NUMBER: P1265232

CATALOG NUMBER: P3AS13R609730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.9	10.0
10°-20°	116.7	26.0
20°-30°	133.1	29.6
30°-40°	94.3	21.0
40°-50°	42.8	9.5
50°-60°	9.1	2.0
60°-70°	4.4	1.0
70°-80°	2.7	0.6
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	294.7	65.6
0°-40°	389.1	86.7
0°-60°	441.0	98.2
0°-90°	449.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	449.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	484	
5°	477	45
15°	421	117
25°	292	133
35°	150	94
45°	54	43
55°	7	9
65°	4	4
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1265232

CATALOG NUMBER: P3AS13R609730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	483.5
2.5°	481.8
5°	477.1
7.5°	469.0
10°	457.9
12.5°	442.1
15°	420.8
17.5°	393.9
20°	362.3
22.5°	328.2
25°	292.3
27.5°	255.6
30°	218.9
32.5°	183.9
35°	150.2
37.5°	120.3
40°	93.5
42.5°	70.8
45°	53.8
47.5°	40.1
50°	26.5
52.5°	12.4
55°	6.8
57.5°	6.0
60°	5.5
62.5°	5.1
65°	4.3
67.5°	3.8
70°	3.4
72.5°	3.0
75°	2.6
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)