

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264623

Luminaire Tested: P3AS09R259730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264623
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 258.0 lumens
Efficiency: N/A
Efficacy: 23.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264623

CATALOG NUMBER: P3AS09R259730DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264623

CATALOG NUMBER: P3AS09R259730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61311
5°	59850
10°	55465
15°	49399
20°	42447
25°	36075
30°	29701
35°	23155
40°	16660
45°	10575
50°	6243
55°	4282
60°	3947
65°	3684
70°	3270
75°	2965
80°	2778
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10575 cd/sqm

TEST NUMBER: P1264623

CATALOG NUMBER: P3AS09R259730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.2	9.8
10°-20°	60.4	23.4
20°-30°	68.2	26.5
30°-40°	54.0	20.9
40°-50°	27.3	10.6
50°-60°	10.9	4.2
60°-70°	7.0	2.7
70°-80°	3.8	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	153.9	59.7
0°-40°	207.9	80.6
0°-60°	246.0	95.4
0°-90°	258.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	258.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	280	
5°	272	25
15°	218	60
25°	149	68
35°	86	54
45°	34	27
55°	11	11
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1264623

CATALOG NUMBER: P3AS09R259730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	279.6
1°	279.6
2°	278.7
3°	277.1
4°	274.8
5°	271.9
6°	268.4
7°	264.2
8°	259.7
9°	254.6
10°	249.1
11°	243.0
12°	237.2
13°	230.5
14°	224.0
15°	217.6
17.5°	199.6
20°	181.9
22.5°	165.2
25°	149.1
27.5°	133.4
30°	117.3
32.5°	102.2
35°	86.5
37.5°	72.0
40°	58.2
42.5°	45.3
45°	34.1
47.5°	25.4
50°	18.3
52.5°	13.8
55°	11.2
57.5°	10.3
60°	9.0
62.5°	8.0
65°	7.1
67.5°	6.1
70°	5.1
72.5°	4.5
75°	3.5
77.5°	2.9
80°	2.2
82.5°	1.6
85°	1.0
87.5°	0.3



TEST NUMBER: P1264623

CATALOG NUMBER: P3AS09R259730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)