

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264629

Luminaire Tested: P3AS09R259730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 206.0 lumens
Efficiency: N/A
Efficacy: 18.6 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264629

CATALOG NUMBER: P3AS09R259730DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264629

CATALOG NUMBER: P3AS09R259730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74797
5°	71759
10°	62858
15°	50534
20°	38830
25°	29373
30°	21218
35°	14107
40°	8559
45°	4993
50°	3173
55°	2561
60°	2237
65°	2024
70°	1667
75°	1610
80°	1263
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4993 cd/sqm

TEST NUMBER: P1264629

CATALOG NUMBER: P3AS09R259730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.7	14.4
10°-20°	61.5	29.9
20°-30°	55.7	27.0
30°-40°	33.4	16.2
40°-50°	13.3	6.4
50°-60°	6.1	3.0
60°-70°	3.7	1.8
70°-80°	2.0	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	146.9	71.3
0°-40°	180.3	87.5
0°-60°	199.7	97.0
0°-90°	206.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	206.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	341	
5°	326	30
15°	223	62
25°	121	56
35°	53	33
45°	16	13
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1264629

CATALOG NUMBER: P3AS09R259730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	341.1
1°	341.1
2°	339.5
3°	335.9
4°	331.4
5°	326.0
6°	318.9
7°	310.9
8°	301.6
9°	292.3
10°	282.3
11°	270.7
12°	258.9
13°	247.0
14°	235.1
15°	222.6
17.5°	193.0
20°	166.4
22.5°	142.3
25°	121.4
27.5°	101.8
30°	83.8
32.5°	67.4
35°	52.7
37.5°	40.1
40°	29.9
42.5°	21.8
45°	16.1
47.5°	12.2
50°	9.3
52.5°	7.7
55°	6.7
57.5°	5.8
60°	5.1
62.5°	4.2
65°	3.9
67.5°	3.2
70°	2.6
72.5°	2.2
75°	1.9
77.5°	1.6
80°	1.0
82.5°	0.6
85°	0.6
87.5°	0.3



TEST NUMBER: P1264629

CATALOG NUMBER: P3AS09R259730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)