

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265236

Luminaire Tested: P3AS13R609730DE010 E3DL1WH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1265236  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R609730DE010 E3DL1WH  
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 634.0 lumens  
Efficiency: N/A  
Efficacy: 43.4 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265236  
CATALOG NUMBER: P3AS13R609730DE010 E3DL1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1265236  
 CATALOG NUMBER: P3AS13R609730DE010 E3DL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	160667
5°	157076
10°	147047
15°	131919
20°	113457
25°	93804
30°	74113
35°	55038
40°	37900
45°	23785
50°	13066
55°	7646
60°	6885
65°	5863
70°	5001
75°	5168
80°	4420
85°	4277

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 23785 cd/sqm



TEST NUMBER: P1265236  
 CATALOG NUMBER: P3AS13R609730DE010 E3DL1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	66.4	10.5
10°-20°	161.4	25.5
20°-30°	177.0	27.9
30°-40°	129.0	20.3
40°-50°	60.9	9.6
50°-60°	19.9	3.1
60°-70°	11.3	1.8
70°-80°	6.1	1.0
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	404.9	63.9
0°-40°	533.8	84.2
0°-60°	614.7	97.0
0°-90°	634.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	634.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	733	
5°	714	66
15°	581	161
25°	388	177
35°	206	129
45°	77	61
55°	20	20
65°	11	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1265236  
CATALOG NUMBER: P3AS13R609730DE010 E3DL1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	732.7
2.5°	728.4
5°	713.6
7.5°	690.9
10°	660.4
12.5°	623.8
15°	581.1
17.5°	535.0
20°	486.2
22.5°	436.5
25°	387.7
27.5°	338.9
30°	292.7
32.5°	248.3
35°	205.6
37.5°	167.3
40°	132.4
42.5°	101.9
45°	76.7
47.5°	55.8
50°	38.3
52.5°	25.3
55°	20.0
57.5°	17.4
60°	15.7
62.5°	13.1
65°	11.3
67.5°	9.6
70°	7.8
72.5°	7.0
75°	6.1
77.5°	4.4
80°	3.5
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)