

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264644

Luminaire Tested: P3AS09R309730DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264644
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309730DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 828.0 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264644
CATALOG NUMBER: P3AS09R309730DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1264644
 CATALOG NUMBER: P3AS09R309730DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95	94
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92	90
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	89	88	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88	86	85	85
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85	84	83	82
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	82	81	80	80
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80	79	78	78
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	77	76	76
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	76	75	74	74
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	74	73	72	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	658785
5°	650185
10°	567680
15°	360819
20°	142952
25°	47761
30°	22206
35°	10065
40°	3864
45°	1892
50°	546
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1892 cd/sqm



TEST NUMBER: P1264644
 CATALOG NUMBER: P3AS09R309730DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	270.1	32.6
10°-20°	418.8	50.6
20°-30°	108.0	13.0
30°-40°	25.4	3.1
40°-50°	4.9	0.6
50°-60°	0.5	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	796.8	96.2
0°-40°	822.2	99.3
0°-60°	827.7	100.0
0°-90°	828.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	828.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3004	
5°	2954	270
15°	1589	419
25°	197	108
35°	38	25
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1264644
CATALOG NUMBER: P3AS09R309730DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3004.3
1°	3002.0
2°	2995.0
3°	2986.9
4°	2975.0
5°	2953.8
6°	2919.4
7°	2862.2
8°	2784.1
9°	2682.2
10°	2549.5
11°	2391.7
12°	2219.4
13°	2021.1
14°	1813.4
15°	1589.4
16°	1369.9
17°	1158.4
18°	955.6
19°	769.5
20°	612.6
21°	482.1
22°	379.3
23°	300.2
24°	240.4
25°	197.4
26°	164.6
27°	139.8
28°	120.9
29°	103.5
30°	87.7
32.5°	55.3
35°	37.6
37.5°	23.5
40°	13.5
42.5°	9.0
45°	6.1
47.5°	3.5
50°	1.6
52.5°	0.6
55°	0.6
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3



TEST NUMBER: P1264644
CATALOG NUMBER: P3AS09R309730DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)