

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265237

Luminaire Tested: P3AS13R609730DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265237
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609730DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 917.0 lumens
Efficiency: N/A
Efficacy: 62.8 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265237

CATALOG NUMBER: P3AS13R609730DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1265237

CATALOG NUMBER: P3AS13R609730DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	216540
5°	214483
10°	208235
15°	195098
20°	172682
25°	144444
30°	113207
35°	82128
40°	54645
45°	34050
50°	18422
55°	5314
60°	4956
65°	4514
70°	4488
75°	4406
80°	4420
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 34050 cd/sqm

TEST NUMBER: P1265237

CATALOG NUMBER: P3AS13R609730DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.8	10.0
10°-20°	238.4	26.0
20°-30°	271.8	29.6
30°-40°	192.7	21.0
40°-50°	87.4	9.5
50°-60°	18.5	2.0
60°-70°	8.9	1.0
70°-80°	5.5	0.6
80°-90°	1.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	601.9	65.6
0°-40°	794.6	86.7
0°-60°	900.6	98.2
0°-90°	917.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	917.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	988	
5°	974	92
15°	859	238
25°	597	272
35°	307	193
45°	110	87
55°	14	19
65°	9	9
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1265237

CATALOG NUMBER: P3AS13R609730DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	987.5
2.5°	984.0
5°	974.4
7.5°	957.8
10°	935.2
12.5°	902.9
15°	859.4
17.5°	804.4
20°	740.0
22.5°	670.2
25°	597.0
27.5°	522.1
30°	447.1
32.5°	375.6
35°	306.8
37.5°	245.8
40°	190.9
42.5°	144.7
45°	109.8
47.5°	81.9
50°	54.0
52.5°	25.3
55°	13.9
57.5°	12.2
60°	11.3
62.5°	10.5
65°	8.7
67.5°	7.8
70°	7.0
72.5°	6.1
75°	5.2
77.5°	4.4
80°	3.5
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)