

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265267

Luminaire Tested: P3AS13R659730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265267
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 336.0 lumens
Efficiency: N/A
Efficacy: 23.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265267
CATALOG NUMBER: P3AS13R659730DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1265267
 CATALOG NUMBER: P3AS13R659730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59798
5°	58992
10°	57002
15°	53757
20°	49588
25°	45027
30°	39880
35°	33917
40°	26993
45°	19041
50°	11053
55°	6040
60°	5614
65°	5085
70°	4680
75°	4321
80°	3788
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19041 cd/sqm



TEST NUMBER: P1265267
 CATALOG NUMBER: P3AS13R659730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.2	7.5
10°-20°	66.3	19.7
20°-30°	85.2	25.3
30°-40°	78.8	23.4
40°-50°	47.5	14.1
50°-60°	16.2	4.8
60°-70°	9.8	2.9
70°-80°	5.5	1.6
80°-90°	1.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	176.6	52.6
0°-40°	255.4	76.0
0°-60°	319.2	95.0
0°-90°	336.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	336.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	273	
5°	268	25
15°	237	66
25°	186	85
35°	127	79
45°	61	48
55°	16	16
65°	10	10
75°	5	6
85°	1	2
90°	0	

TEST NUMBER: P1265267
CATALOG NUMBER: P3AS13R659730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	272.7
2.5°	271.4
5°	268.0
7.5°	262.9
10°	256.0
12.5°	247.5
15°	236.8
17.5°	225.3
20°	212.5
22.5°	199.3
25°	186.1
27.5°	172.0
30°	157.5
32.5°	143.0
35°	126.7
37.5°	110.9
40°	94.3
42.5°	77.7
45°	61.4
47.5°	46.5
50°	32.4
52.5°	20.5
55°	15.8
57.5°	14.1
60°	12.8
62.5°	11.1
65°	9.8
67.5°	8.5
70°	7.3
72.5°	6.4
75°	5.1
77.5°	4.3
80°	3.0
82.5°	2.1
85°	1.3
87.5°	0.9
90°	0.0

(END OF REPORT)