

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265293

Luminaire Tested: P3AS13R709730DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265293
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709730DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 877.0 lumens
Efficiency: N/A
Efficacy: 60.1 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265293

CATALOG NUMBER: P3AS13R709730DE010 E3DL1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1265293

CATALOG NUMBER: P3AS13R709730DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94
2	106	101	96	93		104	99	95	92		96	92	90		93	90	88		90	88	86
3	100	93	88	83		98	92	87	82		89	85	81		86	83	80		84	81	79
4	94	86	80	75		93	85	79	75		83	78	74		81	76	73		79	75	72
5	89	80	73	69		87	79	73	68		77	72	68		75	71	67		74	70	66
6	84	74	68	63		82	73	67	63		72	66	62		70	65	62		69	65	61
7	79	69	62	58		78	68	62	58		67	61	57		66	61	57		65	60	57
8	75	65	58	53		74	64	58	53		63	57	53		62	57	53		61	56	53
9	71	60	54	50		70	60	54	50		59	53	49		58	53	49		57	52	49
10	67	57	50	46		66	56	50	46		55	50	46		55	49	46		54	49	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	169789
5°	167752
10°	162901
15°	156005
20°	146126
25°	132758
30°	114676
35°	91390
40°	66553
45°	43756
50°	20503
55°	6308
60°	6096
65°	5863
70°	5578
75°	5931
80°	5556
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 43756 cd/sqm

TEST NUMBER: P1265293

CATALOG NUMBER: P3AS13R709730DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.8	8.2
10°-20°	192.3	21.9
20°-30°	250.0	28.5
30°-40°	212.1	24.2
40°-50°	109.3	12.5
50°-60°	21.1	2.4
60°-70°	11.4	1.3
70°-80°	7.0	0.8
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	514.0	58.6
0°-40°	726.1	82.8
0°-60°	856.5	97.7
0°-90°	877.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	877.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	774	
5°	762	72
15°	687	192
25°	549	250
35°	341	212
45°	141	109
55°	16	21
65°	11	11
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1265293

CATALOG NUMBER: P3AS13R709730DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	774.3
2.5°	771.6
5°	762.1
7.5°	748.1
10°	731.6
12.5°	710.7
15°	687.2
17.5°	658.4
20°	626.2
22.5°	589.6
25°	548.7
27.5°	502.5
30°	452.9
32.5°	398.0
35°	341.4
37.5°	285.7
40°	232.5
42.5°	182.9
45°	141.1
47.5°	103.6
50°	60.1
52.5°	26.1
55°	16.5
57.5°	15.7
60°	13.9
62.5°	13.1
65°	11.3
67.5°	10.5
70°	8.7
72.5°	7.8
75°	7.0
77.5°	5.2
80°	4.4
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)