

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265328

Luminaire Tested: P3AS17R159730DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265328
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159730DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 711.0 lumens
Efficiency: N/A
Efficacy: 33.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265328

CATALOG NUMBER: P3AS17R159730DE010 E3DLP1H

Luminous Intensity Polar Plot



TEST NUMBER: P1265328

CATALOG NUMBER: P3AS17R159730DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	306598
5°	283380
10°	226226
15°	170898
20°	130141
25°	99175
30°	71049
35°	46364
40°	28425
45°	17180
50°	11428
55°	8831
60°	7587
65°	6590
70°	5898
75°	5846
80°	4420
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17180 cd/sqm

TEST NUMBER: P1265328

CATALOG NUMBER: P3AS17R159730DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.0	16.0
10°-20°	210.4	29.6
20°-30°	187.3	26.3
30°-40°	110.8	15.6
40°-50°	45.5	6.4
50°-60°	21.3	3.0
60°-70°	13.0	1.8
70°-80°	6.8	1.0
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	511.8	72.0
0°-40°	622.6	87.6
0°-60°	689.4	97.0
0°-90°	711.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	711.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1398	
5°	1287	114
15°	753	210
25°	410	187
35°	173	111
45°	55	45
55°	23	21
65°	13	13
75°	7	7
85°	1	2
90°	0	

TEST NUMBER: P1265328

CATALOG NUMBER: P3AS17R159730DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1398.2
1°	1394.7
2°	1384.3
3°	1363.6
4°	1328.9
5°	1287.4
6°	1242.3
7°	1189.2
8°	1133.8
9°	1077.2
10°	1016.0
12.5°	876.3
15°	752.8
17.5°	646.6
20°	557.7
22.5°	479.2
25°	409.9
27.5°	342.9
30°	280.6
32.5°	224.0
35°	173.2
37.5°	132.8
40°	99.3
42.5°	73.9
45°	55.4
47.5°	42.7
50°	33.5
52.5°	27.7
55°	23.1
57.5°	19.6
60°	17.3
62.5°	15.0
65°	12.7
67.5°	11.5
70°	9.2
72.5°	8.1
75°	6.9
77.5°	4.6
80°	3.5
82.5°	2.3
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)