

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265366

Luminaire Tested: P3AS17R259730DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265366
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259730DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1470.0 lumens
Efficiency: N/A
Efficacy: 69.3 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265366

CATALOG NUMBER: P3AS17R259730DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1265366

CATALOG NUMBER: P3AS17R259730DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	97	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86	85	85	85
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83	83	83	83
8	95	89	85	83	94	89	85	82	88	84	82	87	84	82	86	83	81	81	81	81
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	82	80	79	79	79
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78	77	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1571650
5°	1457667
10°	1130440
15°	566836
20°	186216
25°	74037
30°	27776
35°	8031
40°	3635
45°	1427
50°	1194
55°	879
60°	1009
65°	1193
70°	769
75°	1017
80°	1515
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 1515 cd/sqm

TEST NUMBER: P1265366

CATALOG NUMBER: P3AS17R259730DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	582.5	39.6
10°-20°	694.9	47.3
20°-30°	156.6	10.7
30°-40°	25.4	1.7
40°-50°	4.6	0.3
50°-60°	2.5	0.2
60°-70°	2.1	0.1
70°-80°	1.3	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1434.0	97.6
0°-40°	1459.4	99.3
0°-60°	1466.5	99.8
0°-90°	1470.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1470.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7167	
5°	6622	582
15°	2497	695
25°	306	157
35°	30	25
45°	5	5
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1265366

CATALOG NUMBER: P3AS17R259730DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	7167.3
1°	7155.7
2°	7098.0
3°	6991.7
4°	6831.2
5°	6622.2
6°	6372.7
7°	6102.5
8°	5792.9
9°	5454.6
10°	5076.9
11°	4641.5
12°	4140.3
13°	3616.0
14°	3053.5
15°	2496.9
17.5°	1422.8
20°	798.0
22.5°	481.6
25°	306.0
27.5°	188.2
30°	109.7
32.5°	57.7
35°	30.0
37.5°	19.6
40°	12.7
42.5°	8.1
45°	4.6
47.5°	3.5
50°	3.5
52.5°	3.5
55°	2.3
57.5°	2.3
60°	2.3
62.5°	2.3
65°	2.3
67.5°	2.3
70°	1.2
72.5°	1.2
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1265366
CATALOG NUMBER: P3AS17R259730DE010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)