

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265368

Luminaire Tested: P3AS17R259730DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259730DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1560.0 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265368
CATALOG NUMBER: P3AS17R259730DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1265368
 CATALOG NUMBER: P3AS17R259730DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	99	99	99	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	96	96	96	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	96	94	93	92
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90	94	92	90	89
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	92	90	88	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	90	88	86	85
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	88	86	84	83
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	86	84	82	81
9	93	87	83	81	92	86	83	80	86	83	80	85	82	80	84	82	80	84	82	80	79
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	83	80	78	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1708482
5°	1582673
10°	1224538
15°	584884
20°	192843
25°	81295
30°	31499
35°	13626
40°	4523
45°	2109
50°	785
55°	421
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2109 cd/sqm



TEST NUMBER: P1265368

CATALOG NUMBER: P3AS17R259730DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	632.0	40.5
10°-20°	718.8	46.1
20°-30°	167.0	10.7
30°-40°	35.0	2.2
40°-50°	5.7	0.4
50°-60°	0.9	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1517.9	97.3
0°-40°	1552.9	99.5
0°-60°	1559.5	100.0
0°-90°	1560.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1560.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7791	
5°	7190	632
15°	2576	719
25°	336	167
35°	51	35
45°	7	6
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1265368
CATALOG NUMBER: P3AS17R259730DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	7791.3
1°	7775.5
2°	7694.6
3°	7580.9
4°	7407.3
5°	7190.1
6°	6911.2
7°	6619.4
8°	6291.9
9°	5922.6
10°	5499.5
11°	5009.1
12°	4446.3
13°	3829.8
14°	3185.0
15°	2576.4
16°	2037.9
17°	1587.7
18°	1248.9
19°	998.9
20°	826.4
21°	690.6
22°	579.8
23°	484.2
24°	405.0
25°	336.0
27.5°	199.1
30°	124.4
32.5°	79.8
35°	50.9
37.5°	30.5
40°	15.8
42.5°	10.2
45°	6.8
47.5°	4.0
50°	2.3
52.5°	1.1
55°	1.1
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.0
72.5°	0.0



TEST NUMBER: P1265368
CATALOG NUMBER: P3AS17R259730DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)