

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264746

Luminaire Tested: P3AS09R459730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264746
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 232.0 lumens
Efficiency: N/A
Efficacy: 20.9 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264746

CATALOG NUMBER: P3AS09R459730DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1264746

CATALOG NUMBER: P3AS09R459730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69095
5°	67532
10°	62301
15°	54166
20°	44501
25°	34623
30°	25574
35°	17989
40°	11221
45°	6078
50°	3275
55°	2829
60°	2544
65°	2179
70°	1859
75°	1949
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6078 cd/sqm

TEST NUMBER: P1264746

CATALOG NUMBER: P3AS09R459730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.4	12.2
10°-20°	66.0	28.4
20°-30°	65.5	28.2
30°-40°	42.2	18.2
40°-50°	16.2	7.0
50°-60°	6.6	2.8
60°-70°	4.2	1.8
70°-80°	2.3	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	159.9	68.9
0°-40°	202.0	87.1
0°-60°	224.9	96.9
0°-90°	232.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	232.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	315	
5°	307	28
15°	239	66
25°	143	65
35°	67	42
45°	20	16
55°	7	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1264746

CATALOG NUMBER: P3AS09R459730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	315.1
2.5°	313.5
5°	306.8
7.5°	295.2
10°	279.8
12.5°	260.5
15°	238.6
17.5°	214.8
20°	190.7
22.5°	166.3
25°	143.1
27.5°	121.2
30°	101.0
32.5°	83.3
35°	67.2
37.5°	52.7
40°	39.2
42.5°	28.3
45°	19.6
47.5°	13.2
50°	9.6
52.5°	8.0
55°	7.4
57.5°	6.4
60°	5.8
62.5°	4.8
65°	4.2
67.5°	3.5
70°	2.9
72.5°	2.6
75°	2.3
77.5°	1.6
80°	1.3
82.5°	1.0
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)