

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264775

Luminaire Tested: P3AS09R509730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264775
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 237.0 lumens
Efficiency: N/A
Efficacy: 21.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264775

CATALOG NUMBER: P3AS09R509730DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264775

CATALOG NUMBER: P3AS09R509730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68920
5°	67070
10°	61856
15°	54393
20°	45504
25°	36099
30°	26485
35°	18203
40°	11565
45°	6450
50°	3514
55°	2944
60°	2544
65°	2335
70°	2052
75°	1864
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6450 cd/sqm

TEST NUMBER: P1264775

CATALOG NUMBER: P3AS09R509730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.2	11.9
10°-20°	66.4	28.0
20°-30°	67.9	28.7
30°-40°	43.0	18.2
40°-50°	17.1	7.2
50°-60°	6.9	2.9
60°-70°	4.4	1.9
70°-80°	2.3	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	162.5	68.6
0°-40°	205.5	86.7
0°-60°	229.6	96.9
0°-90°	237.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	237.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	314	
5°	305	28
15°	240	66
25°	149	68
35°	68	43
45°	21	17
55°	8	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1264775

CATALOG NUMBER: P3AS09R509730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	314.3
2.5°	312.1
5°	304.7
7.5°	293.2
10°	277.8
12.5°	259.5
15°	239.6
17.5°	217.8
20°	195.0
22.5°	172.3
25°	149.2
27.5°	126.1
30°	104.6
32.5°	85.3
35°	68.0
37.5°	53.2
40°	40.4
42.5°	29.8
45°	20.8
47.5°	14.1
50°	10.3
52.5°	8.7
55°	7.7
57.5°	6.7
60°	5.8
62.5°	5.1
65°	4.5
67.5°	3.8
70°	3.2
72.5°	2.6
75°	2.2
77.5°	1.6
80°	1.3
82.5°	1.0
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)