

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264816

Luminaire Tested: P3AS09R609730DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264816
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609730DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 786.0 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264816

CATALOG NUMBER: P3AS09R609730DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1264816

CATALOG NUMBER: P3AS09R609730DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	106		111	109	107	105		105	103	102		101	100	99		98	97	96
2	108	104	100	96		106	102	98	95		99	96	93		96	93	91		93	91	89
3	103	97	92	88		101	96	91	88		93	89	86		91	87	85		88	86	84
4	98	91	85	81		96	90	85	81		88	83	80		86	82	79		84	81	78
5	93	85	80	75		92	84	79	75		83	78	74		81	77	74		79	76	73
6	89	80	74	70		87	79	74	70		78	73	70		77	72	69		75	72	69
7	85	76	70	66		83	75	69	65		74	69	65		72	68	65		71	67	64
8	81	71	65	61		79	71	65	61		70	65	61		69	64	61		68	64	61
9	77	67	62	58		76	67	61	58		66	61	57		65	61	57		64	60	57
10	73	64	58	54		72	63	58	54		63	58	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	205948
5°	194408
10°	189353
15°	185041
20°	172052
25°	153807
30°	117486
35°	67833
40°	26335
45°	10978
50°	2422
55°	382
60°	263
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10978 cd/sqm

TEST NUMBER: P1264816

CATALOG NUMBER: P3AS09R609730DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.4	10.6
10°-20°	227.0	28.9
20°-30°	284.4	36.2
30°-40°	159.0	20.2
40°-50°	30.2	3.8
50°-60°	1.5	0.2
60°-70°	0.3	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	594.8	75.7
0°-40°	753.8	95.9
0°-60°	785.5	99.9
0°-90°	786.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	786.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	939	
5°	883	83
15°	815	227
25°	636	284
35°	253	159
45°	35	30
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1264816

CATALOG NUMBER: P3AS09R609730DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	939.2
1°	935.3
2°	923.1
3°	908.6
4°	895.1
5°	883.2
6°	874.2
7°	866.5
8°	860.7
9°	855.3
10°	850.4
11°	845.6
12°	840.1
13°	833.4
14°	825.4
15°	815.1
16°	802.5
17°	788.4
18°	772.3
19°	754.0
20°	737.3
21°	719.3
22°	700.6
23°	681.0
24°	659.4
25°	635.7
26°	607.7
27°	576.5
28°	541.4
29°	504.2
30°	464.0
31°	423.4
32°	381.7
32.5°	358.8
33°	338.2
34°	295.5
35°	253.4
36°	215.4
37°	175.2
37.5°	156.9
38°	138.9
39°	111.9
40°	92.0
42.5°	55.9
45°	35.4



TEST NUMBER: P1264816

CATALOG NUMBER: P3AS09R609730DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	19.6
50°	7.1
52.5°	1.6
55°	1.0
57.5°	0.6
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)