

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264817

Luminaire Tested: P3AS09R609730DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264817
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609730DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 786.0 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264817
CATALOG NUMBER: P3AS09R609730DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1264817

CATALOG NUMBER: P3AS09R609730DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82	82	82	82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77	77	77	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67	67	67	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63	63	63	63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59	59	59	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	205948
5°	194408
10°	189353
15°	185041
20°	172052
25°	153807
30°	117486
35°	67833
40°	26335
45°	10978
50°	2422
55°	382
60°	263
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10978 cd/sqm



TEST NUMBER: P1264817

CATALOG NUMBER: P3AS09R609730DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.4	10.6
10°-20°	227.0	28.9
20°-30°	284.4	36.2
30°-40°	159.0	20.2
40°-50°	30.2	3.8
50°-60°	1.5	0.2
60°-70°	0.3	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	594.8	75.7
0°-40°	753.8	95.9
0°-60°	785.5	99.9
0°-90°	786.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	786.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	939	
5°	883	83
15°	815	227
25°	636	284
35°	253	159
45°	35	30
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1264817
CATALOG NUMBER: P3AS09R609730DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	939.2
1°	935.3
2°	923.1
3°	908.6
4°	895.1
5°	883.2
6°	874.2
7°	866.5
8°	860.7
9°	855.3
10°	850.4
11°	845.6
12°	840.1
13°	833.4
14°	825.4
15°	815.1
16°	802.5
17°	788.4
18°	772.3
19°	754.0
20°	737.3
21°	719.3
22°	700.6
23°	681.0
24°	659.4
25°	635.7
26°	607.7
27°	576.5
28°	541.4
29°	504.2
30°	464.0
31°	423.4
32°	381.7
32.5°	358.8
33°	338.2
34°	295.5
35°	253.4
36°	215.4
37°	175.2
37.5°	156.9
38°	138.9
39°	111.9
40°	92.0
42.5°	55.9
45°	35.4



TEST NUMBER: P1264817
CATALOG NUMBER: P3AS09R609730DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	19.6
50°	7.1
52.5°	1.6
55°	1.0
57.5°	0.6
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)