

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265466

Luminaire Tested: P3AS17R409730DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1265466  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R409730DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 97CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1345.0 lumens  
Efficiency: N/A  
Efficacy: 63.4 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265466  
CATALOG NUMBER: P3AS17R409730DE010 E3DL1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1265466  
 CATALOG NUMBER: P3AS17R409730DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94	94	94	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	84	84	84	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80	80	80	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	76	76	76	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72	72	72	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65	65	65	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	63	63	63	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	60	60	60	60

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	595150
5°	577855
10°	524395
15°	433215
20°	312507
25°	193293
30°	104649
35°	54074
40°	29398
45°	16467
50°	8256
55°	6193
60°	5570
65°	5396
70°	5193
75°	4914
80°	4420
85°	3019

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16467 cd/sqm



TEST NUMBER: P1265466  
 CATALOG NUMBER: P3AS17R409730DE010 E3DL1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	242.0	18.0
10°-20°	519.6	38.6
20°-30°	370.8	27.6
30°-40°	136.5	10.2
40°-50°	43.0	3.2
50°-60°	14.9	1.1
60°-70°	10.3	0.8
70°-80°	6.1	0.5
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1132.5	84.2
0°-40°	1269.0	94.3
0°-60°	1326.9	98.7
0°-90°	1345.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1345.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2714	
5°	2625	242
15°	1908	520
25°	799	371
35°	202	137
45°	53	43
55°	16	15
65°	10	10
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P1265466  
CATALOG NUMBER: P3AS17R409730DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2714.1
2.5°	2693.3
5°	2625.2
7.5°	2512.1
10°	2355.1
12.5°	2155.4
15°	1908.3
17.5°	1631.2
20°	1339.2
22.5°	1051.7
25°	798.9
27.5°	586.5
30°	413.3
32.5°	289.8
35°	202.0
37.5°	143.2
40°	102.7
42.5°	73.9
45°	53.1
47.5°	35.8
50°	24.2
52.5°	17.3
55°	16.2
57.5°	15.0
60°	12.7
62.5°	11.5
65°	10.4
67.5°	9.2
70°	8.1
72.5°	6.9
75°	5.8
77.5°	4.6
80°	3.5
82.5°	2.3
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)