

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264858

Luminaire Tested: P3AS09R659730DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264858
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659730DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 517.0 lumens
Efficiency: N/A
Efficacy: 46.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264858
CATALOG NUMBER: P3AS09R659730DE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1264858
 CATALOG NUMBER: P3AS09R659730DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92010
5°	90755
10°	87729
15°	82725
20°	76307
25°	69270
30°	61351
35°	52200
40°	41535
45°	29305
50°	17023
55°	9290
60°	8640
65°	7835
70°	7181
75°	6693
80°	5809
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29305 cd/sqm



TEST NUMBER: P1264858
 CATALOG NUMBER: P3AS09R659730DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.8	7.5
10°-20°	102.0	19.7
20°-30°	131.0	25.3
30°-40°	121.2	23.4
40°-50°	73.2	14.2
50°-60°	25.0	4.8
60°-70°	15.0	2.9
70°-80°	8.5	1.6
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	271.8	52.6
0°-40°	393.0	76.0
0°-60°	491.1	95.0
0°-90°	517.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	517.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	420	
5°	412	39
15°	364	102
25°	286	131
35°	195	121
45°	94	73
55°	24	25
65°	15	15
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1264858
CATALOG NUMBER: P3AS09R659730DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	419.6
2.5°	417.6
5°	412.3
7.5°	404.5
10°	394.0
12.5°	380.8
15°	364.4
17.5°	346.7
20°	327.0
22.5°	306.6
25°	286.3
27.5°	264.6
30°	242.3
32.5°	220.0
35°	195.0
37.5°	170.7
40°	145.1
42.5°	119.5
45°	94.5
47.5°	71.6
50°	49.9
52.5°	31.5
55°	24.3
57.5°	21.7
60°	19.7
62.5°	17.1
65°	15.1
67.5°	13.1
70°	11.2
72.5°	9.8
75°	7.9
77.5°	6.6
80°	4.6
82.5°	3.3
85°	2.0
87.5°	1.3
90°	0.0

(END OF REPORT)