

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265525

Luminaire Tested: P3AS17R509730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265525
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 496.0 lumens
Efficiency: N/A
Efficacy: 23.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265525

CATALOG NUMBER: P3AS17R509730DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265525

CATALOG NUMBER: P3AS17R509730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100803
5°	99317
10°	94921
15°	87901
20°	78990
25°	69439
30°	59047
35°	47890
40°	35982
45°	23165
50°	11019
55°	8640
60°	8201
65°	7627
70°	6924
75°	6270
80°	5683
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23165 cd/sqm

TEST NUMBER: P1265525

CATALOG NUMBER: P3AS17R509730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.3	8.5
10°-20°	108.0	21.8
20°-30°	131.2	26.4
30°-40°	111.2	22.4
40°-50°	57.8	11.6
50°-60°	20.8	4.2
60°-70°	14.4	2.9
70°-80°	7.9	1.6
80°-90°	2.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	281.4	56.7
0°-40°	392.7	79.2
0°-60°	471.3	95.0
0°-90°	496.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	496.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	460	
5°	451	42
15°	387	108
25°	287	131
35°	179	111
45°	75	58
55°	23	21
65°	15	14
75°	7	8
85°	2	2
90°	0	

TEST NUMBER: P1265525

CATALOG NUMBER: P3AS17R509730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	459.7
2.5°	458.0
5°	451.2
7.5°	441.0
10°	426.3
12.5°	407.6
15°	387.2
17.5°	364.0
20°	338.5
22.5°	312.5
25°	287.0
27.5°	260.4
30°	233.2
32.5°	206.1
35°	178.9
37.5°	152.3
40°	125.7
42.5°	100.2
45°	74.7
47.5°	49.8
50°	32.3
52.5°	24.9
55°	22.6
57.5°	20.4
60°	18.7
62.5°	16.4
65°	14.7
67.5°	12.5
70°	10.8
72.5°	9.1
75°	7.4
77.5°	5.7
80°	4.5
82.5°	3.4
85°	2.3
87.5°	1.1
90°	0.0

(END OF REPORT)