

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264885

Luminaire Tested: P3AS09R709730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264885
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 231.0 lumens
Efficiency: N/A
Efficacy: 20.8 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264885

CATALOG NUMBER: P3AS09R709730DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264885

CATALOG NUMBER: P3AS09R709730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54184
5°	53181
10°	50144
15°	45517
20°	39810
25°	33583
30°	27498
35°	21335
40°	15257
45°	9675
50°	4810
55°	2944
60°	2544
65°	2335
70°	2052
75°	1864
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9675 cd/sqm

TEST NUMBER: P1264885

CATALOG NUMBER: P3AS09R709730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.5	9.8
10°-20°	55.8	24.2
20°-30°	63.5	27.5
30°-40°	49.7	21.5
40°-50°	24.4	10.6
50°-60°	7.5	3.2
60°-70°	4.5	1.9
70°-80°	2.4	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	141.9	61.4
0°-40°	191.6	82.9
0°-60°	223.4	96.8
0°-90°	231.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	231.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	247	
5°	242	23
15°	200	56
25°	139	64
35°	80	50
45°	31	24
55°	8	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1264885

CATALOG NUMBER: P3AS09R709730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	247.1
2.5°	245.8
5°	241.6
7.5°	234.9
10°	225.2
12.5°	214.0
15°	200.5
17.5°	186.0
20°	170.6
22.5°	154.6
25°	138.8
27.5°	123.4
30°	108.6
32.5°	93.8
35°	79.7
37.5°	66.2
40°	53.3
42.5°	41.5
45°	31.2
47.5°	21.8
50°	14.1
52.5°	9.3
55°	7.7
57.5°	6.7
60°	5.8
62.5°	5.1
65°	4.5
67.5°	3.9
70°	3.2
72.5°	2.6
75°	2.2
77.5°	1.9
80°	1.3
82.5°	1.0
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)