

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265563

Luminaire Tested: P3AS17R559730DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265563
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559730DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 840.0 lumens
Efficiency: N/A
Efficacy: 39.6 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265563
CATALOG NUMBER: P3AS17R559730DE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1265563
 CATALOG NUMBER: P3AS17R559730DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79			
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67			
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55			
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52			
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	228512
5°	222782
10°	207099
15°	184428
20°	156720
25°	126491
30°	96420
35°	68583
40°	45256
45°	26856
50°	15761
55°	9711
60°	8596
65°	7783
70°	6668
75°	5846
80°	5809
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26856 cd/sqm



TEST NUMBER: P1265563
 CATALOG NUMBER: P3AS17R559730DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.0	11.2
10°-20°	225.2	26.8
20°-30°	238.6	28.4
30°-40°	161.2	19.2
40°-50°	70.7	8.4
50°-60°	25.3	3.0
60°-70°	14.8	1.8
70°-80°	7.8	0.9
80°-90°	2.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	557.8	66.4
0°-40°	718.9	85.6
0°-60°	814.9	97.0
0°-90°	840.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	840.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1042	
5°	1012	94
15°	812	225
25°	523	239
35°	256	161
45°	87	71
55°	25	25
65°	15	15
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1265563
CATALOG NUMBER: P3AS17R559730DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1042.1
2.5°	1034.0
5°	1012.1
7.5°	976.3
10°	930.1
12.5°	874.7
15°	812.4
17.5°	743.2
20°	671.6
22.5°	596.6
25°	522.8
27.5°	450.1
30°	380.8
32.5°	315.0
35°	256.2
37.5°	203.1
40°	158.1
42.5°	118.9
45°	86.6
47.5°	63.5
50°	46.2
52.5°	32.3
55°	25.4
57.5°	23.1
60°	19.6
62.5°	17.3
65°	15.0
67.5°	12.7
70°	10.4
72.5°	9.2
75°	6.9
77.5°	5.8
80°	4.6
82.5°	3.5
85°	2.3
87.5°	1.2
90°	0.0

(END OF REPORT)