

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265575

Luminaire Tested: P3AS17R609730DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609730DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1383.0 lumens
Efficiency: N/A
Efficacy: 65.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265575

CATALOG NUMBER: P3AS17R609730DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1265575

CATALOG NUMBER: P3AS17R609730DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88	86	84	82
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	65	61	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	67	62	58	76	67	61	58	66	61	57		65	61	57		64	60	57	56
10	73	64	58	54	72	63	58	54	63	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	362361
5°	342086
10°	333194
15°	325564
20°	302706
25°	270620
30°	206715
35°	119337
40°	46315
45°	19289
50°	4230
55°	650
60°	482
65°	311
70°	385
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19289 cd/sqm

TEST NUMBER: P1265575

CATALOG NUMBER: P3AS17R609730DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.7	10.6
10°-20°	399.5	28.9
20°-30°	500.4	36.2
30°-40°	279.7	20.2
40°-50°	53.1	3.8
50°-60°	2.7	0.2
60°-70°	0.7	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1046.6	75.7
0°-40°	1326.3	95.9
0°-60°	1382.1	99.9
0°-90°	1383.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1383.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1652	
5°	1554	147
15°	1434	399
25°	1118	500
35°	446	280
45°	62	53
55°	2	3
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1265575

CATALOG NUMBER: P3AS17R609730DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1652.5
1°	1645.7
2°	1624.2
3°	1598.8
4°	1575.0
5°	1554.1
6°	1538.2
7°	1524.7
8°	1514.5
9°	1504.9
10°	1496.4
11°	1487.9
12°	1478.3
13°	1466.4
14°	1452.2
15°	1434.1
16°	1412.1
17°	1387.2
18°	1358.9
19°	1326.7
20°	1297.2
21°	1265.6
22°	1232.7
23°	1198.2
24°	1160.3
25°	1118.5
26°	1069.2
27°	1014.4
28°	952.7
29°	887.1
30°	816.4
31°	745.1
32°	671.5
32.5°	631.4
33°	595.2
34°	519.9
35°	445.8
36°	379.0
37°	308.3
37.5°	276.1
38°	244.4
39°	196.9
40°	161.8
42.5°	98.4
45°	62.2



TEST NUMBER: P1265575

CATALOG NUMBER: P3AS17R609730DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	34.5
50°	12.4
52.5°	2.8
55°	1.7
57.5°	1.1
60°	1.1
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)