

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265607

Luminaire Tested: P3AS17R659730DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265607
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659730DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1158.0 lumens
Efficiency: N/A
Efficacy: 54.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265607
CATALOG NUMBER: P3AS17R659730DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1265607
 CATALOG NUMBER: P3AS17R659730DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63			63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58			58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	273092
5°	269821
10°	259559
15°	243157
20°	218699
25°	185696
30°	145238
35°	103517
40°	67727
45°	41865
50°	21253
55°	7493
60°	6578
65°	6590
70°	5898
75°	5846
80°	5809
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 41865 cd/sqm



TEST NUMBER: P1265607
 CATALOG NUMBER: P3AS17R659730DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.1	9.9
10°-20°	298.1	25.7
20°-30°	348.4	30.1
30°-40°	243.5	21.0
40°-50°	107.2	9.3
50°-60°	23.8	2.1
60°-70°	12.1	1.0
70°-80°	7.3	0.6
80°-90°	2.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	761.6	65.8
0°-40°	1005.0	86.8
0°-60°	1136.0	98.1
0°-90°	1158.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1158.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1245	
5°	1226	115
15°	1071	298
25°	768	348
35°	387	243
45°	135	107
55°	20	24
65°	13	12
75°	7	7
85°	2	3
90°	0	



TEST NUMBER: P1265607
CATALOG NUMBER: P3AS17R659730DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1245.4
2.5°	1240.8
5°	1225.8
7.5°	1200.4
10°	1165.7
12.5°	1123.0
15°	1071.1
17.5°	1007.6
20°	937.2
22.5°	857.6
25°	767.5
27.5°	672.9
30°	573.6
32.5°	477.8
35°	386.7
37.5°	307.0
40°	236.6
42.5°	178.9
45°	135.0
47.5°	99.3
50°	62.3
52.5°	32.3
55°	19.6
57.5°	17.3
60°	15.0
62.5°	13.9
65°	12.7
67.5°	10.4
70°	9.2
72.5°	8.1
75°	6.9
77.5°	5.8
80°	4.6
82.5°	3.5
85°	2.3
87.5°	1.2
90°	0.0

(END OF REPORT)