

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264997

Luminaire Tested: P3AS13R209730DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264997
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209730DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1092.0 lumens
Efficiency: N/A
Efficacy: 74.8 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264997

CATALOG NUMBER: P3AS13R209730DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1264997

CATALOG NUMBER: P3AS13R209730DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	114	112	110		113	111	110	108		107	106	105		104	103	102		100	100	99
2	112	109	106	104		110	107	105	103		104	102	101		101	100	98		99	98	96
3	109	105	102	99		107	104	101	98		101	99	97		99	97	95		97	95	94
4	106	101	98	95		105	100	97	95		99	96	94		97	95	93		95	93	92
5	104	98	95	92		102	98	94	92		96	93	91		95	92	90		93	91	90
6	101	96	92	89		100	95	92	89		94	91	89		93	90	88		92	89	88
7	99	93	90	87		98	93	89	87		92	89	86		91	88	86		90	87	86
8	97	91	87	85		96	91	87	85		90	87	85		89	86	84		88	86	84
9	95	89	85	83		94	89	85	83		88	85	83		87	84	83		87	84	82
10	93	87	84	81		92	87	83	81		86	83	81		86	83	81		85	83	81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1656468
5°	1394670
10°	871104
15°	325677
20°	111776
25°	46599
30°	21953
35°	9824
40°	4637
45°	2388
50°	887
55°	153
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2388 cd/sqm

TEST NUMBER: P1264997

CATALOG NUMBER: P3AS13R209730DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	526.9	48.3
10°-20°	434.0	39.7
20°-30°	98.6	9.0
30°-40°	25.1	2.3
40°-50°	6.3	0.6
50°-60°	0.8	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1059.5	97.0
0°-40°	1084.6	99.3
0°-60°	1091.7	100.0
0°-90°	1092.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1092.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7554	
5°	6336	527
15°	1435	434
25°	193	99
35°	37	25
45°	8	6
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1264997

CATALOG NUMBER: P3AS13R209730DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	7554.1
1°	7490.1
2°	7301.4
3°	7030.7
4°	6698.5
5°	6336.0
6°	5932.1
7°	5486.4
8°	4966.4
9°	4451.0
10°	3912.2
11°	3338.8
12°	2766.2
13°	2281.2
14°	1817.6
15°	1434.6
16°	1132.3
17°	893.2
18°	717.7
19°	583.6
20°	479.0
21°	400.5
22°	334.3
23°	277.9
24°	231.8
25°	192.6
27.5°	126.0
30°	86.7
32.5°	53.4
35°	36.7
37.5°	23.5
40°	16.2
42.5°	11.1
45°	7.7
47.5°	5.1
50°	2.6
52.5°	1.3
55°	0.4
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1264997

CATALOG NUMBER: P3AS13R209730DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)