

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265612

Luminaire Tested: P3AS17R659730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265612
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 446.0 lumens
Efficiency: N/A
Efficacy: 21.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265612

CATALOG NUMBER: P3AS17R659730DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265612

CATALOG NUMBER: P3AS17R659730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79358
5°	78296
10°	75683
15°	71374
20°	65829
25°	59762
30°	52920
35°	45026
40°	35839
45°	25305
50°	14669
55°	8028
60°	7456
65°	6745
70°	6155
75°	5761
80°	5051
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25305 cd/sqm

TEST NUMBER: P1265612

CATALOG NUMBER: P3AS17R659730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.5	7.5
10°-20°	88.0	19.7
20°-30°	113.0	25.3
30°-40°	104.6	23.4
40°-50°	63.1	14.2
50°-60°	21.5	4.8
60°-70°	12.9	2.9
70°-80°	7.3	1.6
80°-90°	2.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	234.4	52.6
0°-40°	339.0	76.0
0°-60°	423.7	95.0
0°-90°	446.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	446.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	362	
5°	356	33
15°	314	88
25°	247	113
35°	168	105
45°	82	63
55°	21	22
65°	13	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1265612

CATALOG NUMBER: P3AS17R659730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	361.9
2.5°	360.2
5°	355.7
7.5°	348.9
10°	339.9
12.5°	328.5
15°	314.4
17.5°	299.1
20°	282.1
22.5°	264.5
25°	247.0
27.5°	228.3
30°	209.0
32.5°	189.8
35°	168.2
37.5°	147.3
40°	125.2
42.5°	103.1
45°	81.6
47.5°	61.7
50°	43.0
52.5°	27.2
55°	21.0
57.5°	18.7
60°	17.0
62.5°	14.7
65°	13.0
67.5°	11.3
70°	9.6
72.5°	8.5
75°	6.8
77.5°	5.7
80°	4.0
82.5°	2.8
85°	1.7
87.5°	1.1
90°	0.0

(END OF REPORT)