

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265013

Luminaire Tested: P3AS13R209730DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209730DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 902.0 lumens
Efficiency: N/A
Efficacy: 61.8 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265013

CATALOG NUMBER: P3AS13R209730DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1265013

CATALOG NUMBER: P3AS13R209730DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86		91	88	85		89	86	84	83
5	98	91	87	83	97	90	86	83	89	85	82		87	84	81		86	83	81	79
6	95	87	83	79	93	87	82	79	85	81	78		84	81	78		83	80	77	76
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		78	74	72	71
9	85	78	73	70	85	77	73	70	77	73	70		76	72	69		75	72	69	68
10	83	75	71	68	82	75	70	67	74	70	67		73	70	67		73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	693979
5°	630837
10°	466235
15°	288424
20°	164701
25°	94022
30°	52742
35°	28697
40°	15715
45°	8652
50°	5049
55°	3670
60°	3421
65°	3165
70°	2821
75°	2965
80°	2147
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8652 cd/sqm

TEST NUMBER: P1265013

CATALOG NUMBER: P3AS13R209730DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.2	27.5
10°-20°	354.3	39.3
20°-30°	184.9	20.5
30°-40°	71.5	7.9
40°-50°	23.2	2.6
50°-60°	9.1	1.0
60°-70°	6.0	0.7
70°-80°	3.6	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	787.4	87.3
0°-40°	858.9	95.2
0°-60°	891.2	98.8
0°-90°	902.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	902.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3165	
5°	2866	248
15°	1270	354
25°	389	185
35°	107	72
45°	28	23
55°	10	9
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1265013

CATALOG NUMBER: P3AS13R209730DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3164.8
1°	3158.7
2°	3121.3
3°	3063.8
4°	2974.9
5°	2865.9
6°	2737.0
7°	2594.1
8°	2428.5
9°	2267.3
10°	2093.9
12.5°	1664.3
15°	1270.5
17.5°	950.7
20°	705.8
22.5°	522.8
25°	388.6
27.5°	286.7
30°	208.3
32.5°	150.7
35°	107.2
37.5°	77.6
40°	54.9
42.5°	39.2
45°	27.9
47.5°	20.0
50°	14.8
52.5°	11.3
55°	9.6
57.5°	8.7
60°	7.8
62.5°	7.0
65°	6.1
67.5°	5.2
70°	4.4
72.5°	4.4
75°	3.5
77.5°	2.6
80°	1.7
82.5°	1.7
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)