

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265625

Luminaire Tested: P3AS17R709730DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265625
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709730DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1444.0 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265625

CATALOG NUMBER: P3AS17R709730DE010 E3CB1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1265625

CATALOG NUMBER: P3AS17R709730DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	286731
5°	273607
10°	260316
15°	253350
20°	243995
25°	230941
30°	214793
35°	180425
40°	116304
45°	54052
50°	14157
55°	3517
60°	3552
65°	3009
70°	2949
75°	2965
80°	2904
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 54052 cd/sqm

TEST NUMBER: P1265625

CATALOG NUMBER: P3AS17R709730DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.4	8.1
10°-20°	313.6	21.7
20°-30°	438.2	30.3
30°-40°	406.2	28.1
40°-50°	145.6	10.1
50°-60°	12.3	0.9
60°-70°	6.1	0.4
70°-80°	4.0	0.3
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	868.1	60.1
0°-40°	1274.3	88.2
0°-60°	1432.3	99.2
0°-90°	1444.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1444.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1308	
5°	1243	116
15°	1116	314
25°	954	438
35°	674	406
45°	174	146
55°	9	12
65°	6	6
75°	4	4
85°	1	2
90°	0	

TEST NUMBER: P1265625

CATALOG NUMBER: P3AS17R709730DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1307.6
2.5°	1288.0
5°	1243.0
7.5°	1201.5
10°	1169.1
12.5°	1142.6
15°	1116.0
17.5°	1083.7
20°	1045.6
22.5°	1001.8
25°	954.5
27.5°	906.0
30°	848.3
32.5°	774.4
35°	674.0
37.5°	545.9
40°	406.3
42.5°	277.0
45°	174.3
47.5°	96.9
50°	41.5
52.5°	13.8
55°	9.2
57.5°	8.1
60°	8.1
62.5°	6.9
65°	5.8
67.5°	5.8
70°	4.6
72.5°	4.6
75°	3.5
77.5°	3.5
80°	2.3
82.5°	2.3
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)