

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265634

Luminaire Tested: P3AS17R709730DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265634
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709730DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1377.0 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265634
CATALOG NUMBER: P3AS17R709730DE010 E3D1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1265634
 CATALOG NUMBER: P3AS17R709730DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			79
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			57
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	267742
5°	252454
10°	239385
15°	235075
20°	226610
25°	213593
30°	212083
35°	184708
40°	119481
45°	56471
50°	7914
55°	650
60°	482
65°	571
70°	385
75°	508
80°	758
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 56471 cd/sqm



TEST NUMBER: P1265634
 CATALOG NUMBER: P3AS17R709730DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.1	7.8
10°-20°	290.8	21.1
20°-30°	411.4	29.9
30°-40°	413.4	30.0
40°-50°	148.7	10.8
50°-60°	4.0	0.3
60°-70°	0.9	0.1
70°-80°	0.6	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	809.3	58.8
0°-40°	1222.7	88.8
0°-60°	1375.4	99.9
0°-90°	1377.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1377.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1221	
5°	1147	107
15°	1036	291
25°	883	411
35°	690	413
45°	182	149
55°	2	4
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1265634
CATALOG NUMBER: P3AS17R709730DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1221.0
1°	1217.6
2°	1206.9
3°	1189.9
4°	1168.4
5°	1146.9
6°	1126.6
7°	1110.7
8°	1096.6
9°	1085.3
10°	1075.1
11°	1066.6
12°	1058.7
13°	1050.8
14°	1043.4
15°	1035.5
16°	1025.9
17°	1015.7
18°	1003.3
19°	988.0
20°	971.1
21°	952.4
22°	933.7
23°	915.6
24°	898.1
25°	882.8
26°	872.1
27°	863.6
28°	856.8
29°	848.9
30°	837.6
31°	821.2
32°	798.0
32.5°	785.0
33°	767.5
34°	733.0
35°	690.0
36°	642.5
37°	588.7
37.5°	563.9
38°	529.9
39°	469.4
40°	417.4
42.5°	289.0
45°	182.1



TEST NUMBER: P1265634
CATALOG NUMBER: P3AS17R709730DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	97.8
50°	23.2
52.5°	2.8
55°	1.7
57.5°	1.7
60°	1.1
62.5°	1.1
65°	1.1
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)