

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265033

Luminaire Tested: P3AS13R259730DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265033
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259730DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 912.0 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265033
CATALOG NUMBER: P3AS13R259730DE010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1265033
 CATALOG NUMBER: P3AS13R259730DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	86	83	81	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	85	82	79	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	82	78	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	73	70	67	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	585019
5°	545805
10°	437222
15°	296801
20°	179589
25°	105006
30°	59807
35°	32899
40°	17461
45°	9179
50°	5356
55°	4014
60°	3421
65°	3632
70°	3334
75°	2965
80°	2147
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9179 cd/sqm



TEST NUMBER: P1265033
 CATALOG NUMBER: P3AS13R259730DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.0	24.1
10°-20°	359.4	39.4
20°-30°	205.4	22.5
30°-40°	81.0	8.9
40°-50°	24.8	2.7
50°-60°	9.8	1.1
60°-70°	6.6	0.7
70°-80°	3.7	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	784.9	86.1
0°-40°	865.9	94.9
0°-60°	900.6	98.7
0°-90°	912.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	912.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2668	
5°	2480	220
15°	1307	359
25°	434	205
35°	123	81
45°	30	25
55°	10	10
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1265033
CATALOG NUMBER: P3AS13R259730DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2667.9
1°	2662.6
2°	2640.9
3°	2602.5
4°	2549.3
5°	2479.6
6°	2397.7
7°	2305.3
8°	2198.1
9°	2088.3
10°	1963.6
11°	1840.8
12°	1705.7
13°	1572.3
14°	1435.5
15°	1307.4
17.5°	1013.6
20°	769.6
22.5°	577.9
25°	434.0
27.5°	321.6
30°	236.2
32.5°	170.8
35°	122.9
37.5°	87.2
40°	61.0
42.5°	41.8
45°	29.6
47.5°	20.9
50°	15.7
52.5°	12.2
55°	10.5
57.5°	9.6
60°	7.8
62.5°	7.0
65°	7.0
67.5°	6.1
70°	5.2
72.5°	4.4
75°	3.5
77.5°	2.6
80°	1.7
82.5°	1.7
85°	0.9
87.5°	0.9



TEST NUMBER: P1265033
CATALOG NUMBER: P3AS13R259730DE010 E3DL1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)