

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265034

Luminaire Tested: P3AS13R259730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265034
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 343.0 lumens
Efficiency: N/A
Efficacy: 23.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265034

CATALOG NUMBER: P3AS13R259730DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265034

CATALOG NUMBER: P3AS13R259730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81529
5°	79573
10°	73746
15°	65676
20°	56448
25°	47979
30°	39500
35°	30758
40°	22127
45°	14048
50°	8324
55°	5735
60°	5263
65°	4877
70°	4360
75°	3982
80°	3788
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14048 cd/sqm

TEST NUMBER: P1265034

CATALOG NUMBER: P3AS13R259730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.5	9.8
10°-20°	80.3	23.4
20°-30°	90.7	26.5
30°-40°	71.8	20.9
40°-50°	36.3	10.6
50°-60°	14.5	4.2
60°-70°	9.3	2.7
70°-80°	5.1	1.5
80°-90°	1.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	204.6	59.6
0°-40°	276.3	80.6
0°-60°	327.2	95.4
0°-90°	343.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	343.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	372	
5°	362	34
15°	289	80
25°	198	91
35°	115	72
45°	45	36
55°	15	15
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1265034

CATALOG NUMBER: P3AS13R259730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	371.8
1°	371.8
2°	370.5
3°	368.3
4°	365.3
5°	361.5
6°	356.8
7°	351.2
8°	345.3
9°	338.4
10°	331.2
11°	323.0
12°	315.4
13°	306.4
14°	297.8
15°	289.3
17.5°	265.4
20°	241.9
22.5°	219.6
25°	198.3
27.5°	177.3
30°	156.0
32.5°	135.9
35°	114.9
37.5°	95.7
40°	77.3
42.5°	60.3
45°	45.3
47.5°	33.8
50°	24.4
52.5°	18.4
55°	15.0
57.5°	13.7
60°	12.0
62.5°	10.7
65°	9.4
67.5°	8.1
70°	6.8
72.5°	6.0
75°	4.7
77.5°	3.8
80°	3.0
82.5°	2.1
85°	1.3
87.5°	0.4



TEST NUMBER: P1265034

CATALOG NUMBER: P3AS13R259730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)