

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265646

Luminaire Tested: P3AS17R709730DE010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1265646  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R709730DE010 E3DLP1WMH  
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 830.0 lumens  
Efficiency: N/A  
Efficacy: 39.2 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265646

CATALOG NUMBER: P3AS17R709730DE010 E3DLP1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1265646

CATALOG NUMBER: P3AS17R709730DE010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 104 | 110 | 107 | 105 | 103 | 103 | 101 | 100 |  | 100 | 98  | 97  |  | 96  |
| 2   | 106 | 101 | 97  | 93  | 104 | 99  | 95  | 92  | 96  | 93  | 90  |  | 93  | 90  | 88  |  | 90  |
| 3   | 100 | 93  | 88  | 83  | 98  | 92  | 87  | 83  | 89  | 85  | 81  |  | 87  | 83  | 80  |  | 84  |
| 4   | 95  | 86  | 80  | 76  | 93  | 85  | 80  | 75  | 83  | 78  | 74  |  | 81  | 77  | 73  |  | 79  |
| 5   | 89  | 80  | 74  | 69  | 88  | 79  | 73  | 69  | 78  | 72  | 68  |  | 76  | 71  | 68  |  | 74  |
| 6   | 85  | 75  | 68  | 64  | 83  | 74  | 68  | 64  | 73  | 67  | 63  |  | 71  | 66  | 63  |  | 70  |
| 7   | 80  | 70  | 64  | 59  | 79  | 69  | 63  | 59  | 68  | 62  | 58  |  | 67  | 62  | 58  |  | 66  |
| 8   | 76  | 66  | 59  | 55  | 75  | 65  | 59  | 55  | 64  | 58  | 54  |  | 63  | 58  | 54  |  | 62  |
| 9   | 72  | 62  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 55  | 51  |  | 59  | 54  | 51  |  | 58  |
| 10  | 69  | 58  | 52  | 48  | 67  | 58  | 52  | 48  | 57  | 51  | 48  |  | 56  | 51  | 48  |  | 55  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 194677 |
| 5°  | 191107 |
| 10° | 180202 |
| 15° | 163542 |
| 20° | 143069 |
| 25° | 120684 |
| 30° | 98800  |
| 35° | 76640  |
| 40° | 54874  |
| 45° | 34732  |
| 50° | 17330  |
| 55° | 10590  |
| 60° | 9122   |
| 65° | 8406   |
| 70° | 7373   |
| 75° | 6863   |
| 80° | 5809   |
| 85° | 5787   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 34732 cd/sqm

TEST NUMBER: P1265646

CATALOG NUMBER: P3AS17R709730DE010 E3DLP1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 81.0   | 9.8       |
| 10°-20°   | 200.5  | 24.2      |
| 20°-30°   | 228.3  | 27.5      |
| 30°-40°   | 178.5  | 21.5      |
| 40°-50°   | 87.7   | 10.6      |
| 50°-60°   | 27.0   | 3.2       |
| 60°-70°   | 16.0   | 1.9       |
| 70°-80°   | 8.5    | 1.0       |
| 80°-90°   | 2.5    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 509.8  | 61.4      |
| 0°-40°    | 688.3  | 82.9      |
| 0°-60°    | 803.0  | 96.7      |
| 0°-90°    | 830.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 830.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 888 |      |
| 5°  | 868 | 81   |
| 15° | 720 | 200  |
| 25° | 499 | 228  |
| 35° | 286 | 179  |
| 45° | 112 | 88   |
| 55° | 28  | 27   |
| 65° | 16  | 16   |
| 75° | 8   | 9    |
| 85° | 2   | 3    |
| 90° | 0   |      |

TEST NUMBER: P1265646

CATALOG NUMBER: P3AS17R709730DE010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 887.8 |
| 2.5°  | 883.2 |
| 5°    | 868.2 |
| 7.5°  | 844.0 |
| 10°   | 809.3 |
| 12.5° | 768.9 |
| 15°   | 720.4 |
| 17.5° | 668.5 |
| 20°   | 613.1 |
| 22.5° | 555.3 |
| 25°   | 498.8 |
| 27.5° | 443.3 |
| 30°   | 390.2 |
| 32.5° | 337.1 |
| 35°   | 286.3 |
| 37.5° | 237.8 |
| 40°   | 191.7 |
| 42.5° | 148.9 |
| 45°   | 112.0 |
| 47.5° | 78.5  |
| 50°   | 50.8  |
| 52.5° | 33.5  |
| 55°   | 27.7  |
| 57.5° | 24.2  |
| 60°   | 20.8  |
| 62.5° | 18.5  |
| 65°   | 16.2  |
| 67.5° | 13.9  |
| 70°   | 11.5  |
| 72.5° | 9.2   |
| 75°   | 8.1   |
| 77.5° | 6.9   |
| 80°   | 4.6   |
| 82.5° | 3.5   |
| 85°   | 2.3   |
| 87.5° | 1.2   |
| 90°   | 0.0   |

(END OF REPORT)