

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265072

Luminaire Tested: P3AS13R309730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265072
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 275.0 lumens
Efficiency: N/A
Efficacy: 18.8 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265072

CATALOG NUMBER: P3AS13R309730DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1265072

CATALOG NUMBER: P3AS13R309730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	53		61	57	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	93962
5°	91041
10°	82029
15°	67855
20°	52528
25°	39414
30°	28612
35°	19060
40°	11708
45°	6884
50°	4230
55°	3441
60°	2982
65°	2439
70°	2180
75°	2203
80°	1642
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6884 cd/sqm

TEST NUMBER: P1265072

CATALOG NUMBER: P3AS13R309730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.0	13.8
10°-20°	82.3	29.9
20°-30°	74.9	27.2
30°-40°	45.3	16.5
40°-50°	18.1	6.6
50°-60°	8.1	2.9
60°-70°	4.8	1.8
70°-80°	2.7	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	195.3	71.0
0°-40°	240.6	87.5
0°-60°	266.8	97.0
0°-90°	275.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	275.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	428	
5°	414	38
15°	299	82
25°	163	75
35°	71	45
45°	22	18
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1265072

CATALOG NUMBER: P3AS13R309730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	428.5
1°	428.1
2°	426.4
3°	423.4
4°	419.2
5°	413.6
6°	406.8
7°	399.6
8°	390.2
9°	379.5
10°	368.4
11°	355.6
12°	342.0
13°	328.3
14°	313.4
15°	298.9
17.5°	261.0
20°	225.1
22.5°	191.9
25°	162.9
27.5°	136.5
30°	113.0
32.5°	91.3
35°	71.2
37.5°	54.6
40°	40.9
42.5°	29.8
45°	22.2
47.5°	16.6
50°	12.4
52.5°	9.8
55°	9.0
57.5°	7.7
60°	6.8
62.5°	5.5
65°	4.7
67.5°	4.3
70°	3.4
72.5°	3.0
75°	2.6
77.5°	2.1
80°	1.3
82.5°	0.9
85°	0.9
87.5°	0.4



TEST NUMBER: P1265072
CATALOG NUMBER: P3AS13R309730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)