

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265724

Luminaire Tested: P3AS20R209730D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265724
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R209730D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1900.0 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265724

CATALOG NUMBER: P3AS20R209730D010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1265724

CATALOG NUMBER: P3AS20R209730D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	114	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	105	103	104	102	101		101	100	98		99
3	109	105	102	99	107	104	101	98	101	99	97		99	97	95		97
4	106	101	98	95	105	100	97	95	99	96	94		97	95	93		95
5	104	98	95	92	102	98	94	92	96	93	91		95	92	90		93
6	101	96	92	89	100	95	92	89	94	91	89		93	90	88		92
7	99	93	90	87	98	93	89	87	92	89	86		91	88	86		90
8	97	91	87	85	96	91	87	85	90	87	85		89	86	84		88
9	95	89	85	83	94	89	85	83	88	85	83		87	84	83		87
10	93	87	84	81	92	87	83	81	86	83	81		86	83	81		85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2882138
5°	2426628
10°	1515648
15°	566655
20°	194500
25°	81053
30°	38183
35°	17106
40°	8072
45°	4155
50°	1535
55°	268
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4155 cd/sqm

TEST NUMBER: P1265724

CATALOG NUMBER: P3AS20R209730D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	916.8	48.3
10°-20°	755.1	39.7
20°-30°	171.6	9.0
30°-40°	43.7	2.3
40°-50°	11.0	0.6
50°-60°	1.4	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1843.5	97.0
0°-40°	1887.2	99.3
0°-60°	1899.5	100.0
0°-90°	1900.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1900.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13144	
5°	11024	917
15°	2496	755
25°	335	172
35°	64	44
45°	13	11
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1265724

CATALOG NUMBER: P3AS20R209730D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	13143.6
1°	13032.2
2°	12703.9
3°	12232.9
4°	11654.9
5°	11024.2
6°	10321.5
7°	9545.9
8°	8641.1
9°	7744.4
10°	6806.9
11°	5809.3
12°	4813.1
13°	3969.2
14°	3162.4
15°	2496.1
16°	1970.1
17°	1554.1
18°	1248.8
19°	1015.5
20°	833.5
21°	696.8
22°	581.7
23°	483.6
24°	403.4
25°	335.0
27.5°	219.1
30°	150.8
32.5°	92.9
35°	63.9
37.5°	40.9
40°	28.2
42.5°	19.3
45°	13.4
47.5°	8.9
50°	4.5
52.5°	2.2
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1265724

CATALOG NUMBER: P3AS20R209730D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)