

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265750

Luminaire Tested: P3AS20R259730D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265750
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R259730D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2049.0 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265750

CATALOG NUMBER: P3AS20R259730D010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1265750

CATALOG NUMBER: P3AS20R259730D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		100
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		98
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	106	101	97	94	104	100	96	94	98	95	92		96	93	91		94
5	103	97	93	91	101	96	93	90	95	92	90		93	91	89		92
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		90
7	98	92	88	85	97	91	87	85	90	87	84		89	86	84		88
8	95	89	85	83	94	89	85	83	88	85	82		87	84	82		86
9	93	87	83	81	92	86	83	80	86	83	80		85	82	80		84
10	91	85	81	79	90	84	81	79	84	81	78		83	80	78		83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2244031
5°	2078775
10°	1608365
15°	768222
20°	253282
25°	106772
30°	41373
35°	17909
40°	5954
45°	2760
50°	1023
55°	573
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2760 cd/sqm

TEST NUMBER: P1265750

CATALOG NUMBER: P3AS20R259730D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	830.1	40.5
10°-20°	944.1	46.1
20°-30°	219.4	10.7
30°-40°	46.0	2.2
40°-50°	7.4	0.4
50°-60°	1.2	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1993.6	97.3
0°-40°	2039.7	99.5
0°-60°	2048.4	100.0
0°-90°	2049.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2049.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10234	
5°	9444	830
15°	3384	944
25°	441	219
35°	67	46
45°	9	7
55°	2	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1265750

CATALOG NUMBER: P3AS20R259730D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	10233.6
1°	10212.8
2°	10106.6
3°	9957.3
4°	9729.2
5°	9443.9
6°	9077.7
7°	8694.3
8°	8264.2
9°	7779.0
10°	7223.3
11°	6579.2
12°	5840.0
13°	5030.3
14°	4183.3
15°	3384.0
16°	2676.7
17°	2085.4
18°	1640.4
19°	1312.0
20°	1085.4
21°	907.1
22°	761.5
23°	635.9
24°	531.9
25°	441.3
27.5°	261.5
30°	163.4
32.5°	104.8
35°	66.9
37.5°	40.1
40°	20.8
42.5°	13.4
45°	8.9
47.5°	5.2
50°	3.0
52.5°	1.5
55°	1.5
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.0
72.5°	0.0



TEST NUMBER: P1265750

CATALOG NUMBER: P3AS20R259730D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)