

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265197

Luminaire Tested: P3AS13R559730DE010 E3CD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265197
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559730DE010 E3CD1MW
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1160.0 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265197
CATALOG NUMBER: P3AS13R559730DE010 E3CD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1265197

CATALOG NUMBER: P3AS13R559730DE010 E3CD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94	94	94	94
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89	89	89	89
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84	84	84	84
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	86	83	80	79	79	79	79
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76	74	74	74	74
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70	70	70	70
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66	66	66	66
8	83	74	69	65	82	74	69	65	73	68	65	72	67	64	71	67	64	63	63	63	63
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61	60	60	60	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57	57	57	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	321729
5°	318731
10°	331546
15°	326949
20°	301493
25°	245313
30°	149010
35°	51584
40°	14713
45°	7039
50°	2968
55°	1338
60°	1535
65°	1349
70°	1090
75°	1440
80°	1137
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7039 cd/sqm



TEST NUMBER: P1265197
 CATALOG NUMBER: P3AS13R559730DE010 E3CD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.0	12.1
10°-20°	400.3	34.5
20°-30°	446.2	38.5
30°-40°	146.0	12.6
40°-50°	19.2	1.7
50°-60°	4.1	0.4
60°-70°	2.3	0.2
70°-80°	1.5	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	986.5	85.0
0°-40°	1132.5	97.6
0°-60°	1155.8	99.6
0°-90°	1160.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1160.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1467	
5°	1448	140
15°	1440	400
25°	1014	446
35°	193	146
45°	23	19
55°	4	4
65°	3	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1265197
CATALOG NUMBER: P3AS13R559730DE010 E3CD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1467.2
2.5°	1456.8
5°	1448.0
7.5°	1469.0
10°	1489.0
12.5°	1478.5
15°	1440.2
17.5°	1379.2
20°	1292.0
22.5°	1171.7
25°	1013.9
27.5°	813.4
30°	588.5
32.5°	360.9
35°	192.7
37.5°	97.6
40°	51.4
42.5°	33.1
45°	22.7
47.5°	15.7
50°	8.7
52.5°	5.2
55°	3.5
57.5°	3.5
60°	3.5
62.5°	2.6
65°	2.6
67.5°	1.7
70°	1.7
72.5°	1.7
75°	1.7
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)